




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ECO-20-012219	11SEP2020	GK	DR

 Listed	 Certified
12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED



- 1 STAMP AMP 12-10* 6-9, S, APPROX AS SHOWN (S IS OPTIONAL)
- 2. WIRE INSULATION DIAMETER: Ø3.810- 6.350 [Ø.150-.250]
- 3. BODY MATERIAL THK: 0.991±0.051 [.039±.002]
- 4 MATERIAL: BODY - CU PER ASTM B152
INSULATION - PVC
- 5 FINISH: BODY - TIN PLATE 0.00254 [.000100] MIN EXT THK PER ASTM B545
INSULATION COLOR - YELLOW
- 6 APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE

100	RT060-100-V	1SET121020R0000	160300
QTY	DESIGNATION	ENTRELEC PN	TE PN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11SEP2020 GOPALAKRISHNA HV	ENTRELEC Electrical Solutions	
DIMENSIONS: mm [INCHES]		CHK 11SEP2020 ROHDE DANIEL F		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 11SEP2020 ROHDE DANIEL F	NAME	
0 PLC ± -		PRODUCT SPEC	TERMINAL, RING TONGUE, PLASTI-GRIP, WIRE SIZE: 12-10 AWG	
1 PLC ± -		APPLICATION SPEC	SIZE	
2 PLC ± -		114-2161	CAGE CODE	DRAWING NO
3 PLC ± 0.127[.005]		WEIGHT	A3	00779
4 PLC ± -		CUSTOMER DRAWING	C-1SET121020R0000	
4 PLC ANGLES ± 1°		SCALE	4:1	SHEET
FINISH		RESTRICTED TO	1	OF 1
- 4		REV	A	
- 5				

MAX RECOMMENDED OPERATING TEMPERATURE:	105°C [221°F]
VOLTAGE RATING:	600V MAX [1000V SIGNS OR FIXTURES]
CIRCULAR MIL AREA:	2.62-6.64mm² [5,180-13,100] SOLID OR STRANDED