



RF CONNECTORS AND CABLE ASSEMBLIES FOR TESTING AND MEASUREMENT APPLICATIONS

TE Connectivity's (TE) high frequency RF connectors, adaptors, termination and testing cable assemblies support up to 110 GHz and can provide better performance for test & measurement and other demanding applications.

This extended RF product line is one of the highest performing in the industry, with low insertion loss and VSWR, and is compatible with other RF vendors. We make it easy to get these products faster, with competitive pricing and faster delivery.

With a standard product offering and custom capabilities, TE can offer high frequency RF products to meet many customer needs. Our broad RF portfolio allows us to provide a range of RF solutions to our customers.

PRODUCT FACTS

Outstanding Performance

- High frequency performance up to 110 GHz
- · Low insertion loss and VSWR
- Amplitude and phase stability

Competitive Price & Fast Delivery

· Our engineering and manufacturing expertise along with our global footprint enable competitive pricing and fast delivery

Broad Portfolio

- Standard portfolio of N-type, SMA-type, BNC, mini-SMB, 3.5mm, 2.92mm, 2.40mm, 1.85mm, and 1.0mm RF connectors, adaptors, termination and testing cable assemblies available
- · Connectors and cable assemblies can be customized to meet many customer needs



RF termination

- Industry leading electrical performance (VSWR, insertion loss) for 2.92mm, SMA-type, N-Type, BNC and mini-SMB termination
- · Compact size



Blind mate adaptors

- Screw-on connection
- · Quicker connection to improve testing efficiency and to help save cost
- · Floating design for alignment
- Rated to 20,000 cycles
- Industry leading signal integrity (SI) performance for 2.40mm, 2.92mm, SMA-type, N-type, BNC and testing probes



Solderless connectors

- Multi-port SMPM RF product
- Up to 70 GHz performance
- Customer can assemble connectors to PCB directly without soldering process to help to save development and production time
- Industry leading SI performance for SMPM, 2.40mm, 2.92MM, and SMA-type solderless connectors
- Vertical and edge launch types.
- Rated to 1,000 cycles



VNA testing cable assemblies

- Used between testing benchtop (such as VNA) and DUT, stable phase and amplitude
- Industry leading SI performance for 1.0mm, 1.85mm, 2.40mm, 3.5mm testing cable assemblies
- Ruggedized cable assemblies have improved mechanical reliability



Waveguide connectors

- Industry leading SI performance for 1.0mm waveguide connectors
- Provide ultra-low loss for signal conversion between rectangular waveguide and coaxial
- Rated to 1,000 cycles

RF CONNECTORS AND CABLE ASSEMBLIES FOR TESTING AND MEASUREMENT APPLICATIONS

VNA adaptors



- Can be used to connect with VNA port to protect VNA
- Can be used to change the VNA port to normal testing adaptors and testing cable assemblies
- Industry leading SI performance for 1.85mm, 2.40mm, 2.92mm VNA adaptors

High power connectors, Low passive intermodulation (PIM) cable assemblies

Connectors

- Outstanding electrical performance
- · Greater locking torque

Cable assemblies

- Outstanding electrical performance(VSWR and Low PIM)
- The tail is injection molded to have better reliability

PART NUMBERS

Part Number	Description	Product Type
2441517-1	2.92mm MALE TERMINATION	RF termination
2441518-1	SMA PLUG 50 OHM FOR LOAD	RF termination
2441519-1	N MALE TERMINATION	RF termination
2441520-1	BNC MALE TERMINATION 75 ohm	RF termination
2441521-1	MINI-SMB 750HMS MALE TERMINATOR	RF termination
2441538-1	SMA FEMALE TO FLOATING BLIND MATE SMA MALE ADAPTER, 50Ω	Blind mate adaptors
2441539-1	2.92mm FEMALE TO 2.92mm MALE (SLIDE-ON) ADAPTOR	Blind mate adaptors
2441542-1	2.4mm FEMALE TO 2.4mm MALE (SLIDE-ON) ADAPTOR	Blind mate adaptors
2441543-1	N FEMALE TO QUICK LOCK N MALE ADAPTER, 50Ω	Blind mate adaptors
2441534-1	ML51 J TO RF SWITCH 6 ADAPTOR	Blind mate adaptors
2441535-1	ML51 J TO RF SWITCH 6 ADAPTOR	Blind mate adaptors
2441545-1	SMA FEMALE S/T FOR PCB MOUNTING,2 HOLES FLANGE ,50 Ω	Solderless connectors
2441546-1	2.92 mm FEMALE S/TFIELD REPLACEABLE, 50Ω	Solderless connectors
2441872-1	2.4mm FEMALE S/T CONNECTOR WITH END LAUNCH, 50Ω	Solderless connectors
2441873-1	2.92 mm FEMALE S/T CONNECTOR WITH END LAUNCH, 50Ω	Solderless connectors
2441483-1	SSMP SB MALE S/T 8-PORT EDGE LAUNCH,50 Ω	Solderless connectors
2441484-1	SSMP FEMALE TO SSMP FEMALE ADAPTOR, 50Ω	Solderless connectors
2441485-1	SSMP FD MALE S/T 8-PORT EDGE LAUNCH,50 Ω	Solderless connectors
2441515-1	WR10-1.0KWAVEGUIDE COAXIAL CONVERTER	Waveguide connectors
2441516-1	WR12-1.0K WAVEGUIDE COAXIAL CONVERTER	Waveguide connectors
2441390-1	2.4mm FEMALE TO 3.5mm FEMALE S/T NMD ADAPTOR ,50 Ω	VNA adaptors
2441417-1	2.4mm FEMALE TO 3.5mm MALE S/T NMD ADAPTOR ,50 Ω	VNA adaptors
2441440-1	2.4mm FEMALE TO 2.92mm MALE S/T NMD ADAPTOR ,50 Ω	VNA adaptors

RF CONNECTORS AND CABLE ASSEMBLIES FOR TESTING AND MEASUREMENT APPLICATIONS

Part Number	Description	Product Type
2441445-1	2.4mm FEMALE TO 2.92mm FEMALE S/T NMD ADAPTOR ,50 Ω	VNA adaptors
2441448-1	2.4mm FEMALE TO 2.4mm MALE S/T NMD ADAPTOR ,50 Ω	VNA adaptors
2441449-1	2.4mm FEMALE TO 2.4mm FEMALE S/T NMD ADAPTOR ,50 Ω	VNA adaptors
2441450-1	1.85mm FEMALE TO 1.85mm FEMALE S/T NMD ADAPTOR ,50 Ω	VNA adaptors
2441451-1	1.85mm MALE TO 1.85mm FEMALE S/T NMD ADAPTOR ,50 Ω	VNA adaptors
<u>2441452-1</u>	2.92 MALE TO 2.92mm FEMALE S/T NMD ADAPTOR ,50 Ω	VNA adaptors
2441453-1	2.92 FEMALE TO 2.92mm FEMALE S/T NMD ADAPTOR ,50 Ω	VNA adaptors
1-2441454-0	NMD 1.85mm FEMALE SIT TO NMD 1.85mm MALE SIT TEST CABLE 1000mm	VNA testing cable assemblies
1-2441456-0	NMD 1.85mm FEMALE SIT TO 1.85mm FEMALE SIT TEST CABLE 1000mm	VNA testing cable assemblies
1-2441460-0	NMD 2.4mm FEMALE S/T TO NMD 2.4mm MALE S/T TEST CABLE 1000mm	VNA testing cable assemblies
1-2441463-0	NMD 2.4mm FEMALE S/T TO 2.4mm FEMALE S/T TEST CABLE 1000mm	VNA testing cable assemblies
1-2441466-0	NMD 2.4mm FEMALE S/T TO NMD 3.5mm MALE S/T TEST CABLE 1000mm	VNA testing cable assemblies
1-2441470-0	NMD 2.4mm FEMALE S/T TO 3.5mm MALE S/T TEST CABLE 1000mm	VNA testing cable assemblies
1-2441474-0	NMD 2.4mm FEMALE S/T TO N MALE S/T TEST CABLE 1000mm	VNA testing cable assemblies
2441454-1	NMD 1.85mm FEMALE SIT TO NMD 1.85mm MALE SIT TEST CABLE 600mm	VNA testing cable assemblies
2441456-1	NMD 1.85mm FEMALE SIT TO 1.85mm FEMALE SIT TEST CABLE 600mm	VNA testing cable assemblies
2441460-1	NMD 2.4mm FEMALE S/T TO NMD 2.4mm MALE S/T TEST CABLE 600 mm	VNA testing cable assemblies
<u>2441463-1</u>	NMD 2.4mm FEMALE S/T TO 2.4mm FEMALE S/T TEST CABLE 600mm	VNA testing cable assemblies
<u>2441466-1</u>	NMD 2.4mm FEMALE S/T TO NMD 3.5mm MALE S/T TEST CABLE 600mm	VNA testing cable assemblies
2441470-1	NMD 2.4mm FEMALE S/T TO 3.5mm MALE S/T TEST CABLE 600mm	VNA testing cable assemblies
2441474-1	NMD 2.4mm FEMALE S/T TO N MALE S/T TEST CABLE 600mm	VNA testing cable assemblies
1-2441478-0	1.0mm MALE S/T TO 1.0mm MALE S/T FOR TEST CABLE WITH 1M	VNA testing cable assemblies
<u>2441478-1</u>	1.0mm MALE S/T TO 1.0mm MALE S/T FOR TEST CABLE WITH 300mm	VNA testing cable assemblies
2441478-2	1.0mm MALE S/T TO 1.0mm MALE S/T FOR TEST CABLE WITH 500mm	VNA testing cable assemblies
<u>2441478-3</u>	1.0mm MALE S/T TO 1.0mm MALE S/T FOR TEST CABLE WITH 600mm	VNA testing cable assemblies
2441529-1	4.3-10 MALE S/T TO 4.3-10 MALE S/T FOR M5458H-3/8 SF CABLE	Connectors for low PIM cable assemblies
2441531-1	7-16 MALE S/T TO 7-16 MALE S/T FOR 1/2 SF CABLE	Connectors for low PIM cable assemblies
2441522-1	7/16 Male(Plug) R/A FOR RG-213/RG-214/RG-393 CABLE	Low PIM cable assemblies
2441524-1	LC Male(Plug) S/T CRIMP FOR HPL-1200 CABLE,50 Ω	Low PIM cable assemblies
2441708-1	EIA 7/8' S/T CLAMP CONNECTOR FOR SFT-600 CABLE,50 Ω	Low PIM cable assemblies

te.com

TE Connectivity, TE and TE connectivity (logo) are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

© 2024 TE Connectivity. All Rights Reserved.

02/24

