




22-16 AWG
SOLID OR STRANDED



1. STAMP AMP 22-18* APPROX AS SHOWN
WIRE RANGE IS 22-16 AWG

2. WIRE INSULATION DIAMETER: $\varnothing 2.667 - 3.556$ [$\varnothing .105 - .140$]

3. BODY MATERIAL THK: 0.787 ± 0.051 [$.031 \pm .002$]

4. MATERIAL: BODY - CU PER ASTM B152
INSULATION - PVC

5. FINISH: BODY - TIN PLATE 0.00254 [$.000100$] MIN EXT THK PER ASTM B545
INSULATION COLOR - RED

6. APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE

100	SDF015-040-V	1SET132002R0000	324169
QTY	DESIGNATION	ENTRELEC PN	TE PN

		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN21SEP2020 GOPALAKRISHNA HV CHK21SEP2020 ROHDE DANIEL F APVD21SEP2020 ROHDE DANIEL F PRODUCT SPEC UL 486A-B APPLICATION SPEC 114-2161 WEIGHT —		ENTRELEC Electrical Solutions NAME TERMINAL, SPADE, FLANGED, PLASTI-GRIP, WIRE SIZE :22-16 AWG SIZECAGE CODEDRAWING NORESTRICTED TO A300779C-1SET132002R0000—						
MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± 0.127[.005] 4 PLC ± — ANGLES ± —								
VOLTAGE RATING: 600V MAX (1000V FIXTURE OR SIGN)												
CIRCULAR MIL AREA: 0.26-1.65mm² [509-3260] SOLID OR STRANDED		MATERIAL 		FINISH 		CUSTOMER DRAWING				SCALE 6:1	SHEET 1 OF 1	REV A