


REVISIONS





P	LTR	DESCRIPTION	DATE	DWN	APVD
A1		REVISED (ECR-13-002791)	15FEB2013	SJ	HG
A2		REVISED (ECR-16-018207)	26DEC2016	SJ	JW
A3		REVISED (ECR-21-117140)	13OCT2021	JU	JC
A4		REVISED (ECR-23-187877)	22SEP2023	SY	KT

TYPE 1
 (A3) 2109258-4
 2109258-5




TYPE 2
 (A3) 1-2109258-8



SCALE 2:1



SCALE 2:1



(A1) Notes

1. GENERAL TOLERANCE: ± 0.3 , $\pm 3^\circ$
2. APPLICABLE MATE PART

PLUG	CAVITY PLUG
2005465 2005475	2109258-4, 1-2109258-8
(A4) (A2) 2005238 1419168	2109258-4
X-1897133-X	2109258-5

TYPE	COLOR	MATERIAL	DISCRIPTION	P/N
2	BLUE	PA66	MCON 1.2 CAVITY PLUG FOR 1.5mm	1-2109258-8
1	YELLOW	PA66	MCON 1.2 CAVITY PLUG FOR 0.75mm	2109258-5
	BROWN	PA66	MCON 1.2 CAVITY PLUG FOR 0.75mm	2109258-4

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
<p>3rd ANGLE PROJECTION</p>	0 PLC \pm
	1 PLC \pm
	2 PLC \pm
	3 PLC \pm
	4 PLC \pm
MATERIAL	FINISH

DWN SJ CHOI
CHK SJ CHOI
APVD JW JUNG
PRODUCT SPEC
APPLICATION SPEC
WEIGHT
CUSTOMER DRAWING

STE TE Connectivity

NAME
MCON 1.2 CAVITY PLUG FOR 0.75mm AND 1.5mm

SIZE A3	CAGE CODE 00779	DRAWING NO C-2109258	RESTRICTED TO -
------------	--------------------	-------------------------	--------------------

SCALE 10:1 SHEET 1 OF 1 REV A4