

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-				
C		REVISED PER ECO 13-001843.	08FEB2013	MGM	CT

SINGLE POLARIZATION

DOUBLE POLARIZATION

CAVITY IDENTIFICATION WHEN VIEWED FROM REAR OF CONNECTOR

POSITION TOLERANCE ±0.2

1 THE PART IS MARKED WITH THE TE PART NUMBER, CHINA, DATE CODE AND LOT ID.

2. DWV RATING: 725VAC @ SEA LEVEL

3. --

4. WORKING TEMPERATURE: -55°C ~ +125°C

5 MATERIAL: CONTACT : COPPER ALLOY  
 SHELL : COPPER ALLOY  
 INSULATOR : PEEK

6 FINISH: CONTACT: GOLD OVER NICKEL  
 SHELL : BLACK CHROMIUM

7. MAX WIRE SIZE - 24AWG

8 ALL TOLERANCES TO BE ±0.20MM UNLESS NOTED.

CHROMIUM-BLACK	DOUBLE	SOLDER CUP	ø12	ø12	ø13	38.6	ø15	ø18	4	2157344-2
CHROMIUM-BLACK	SINGLE	SOLDER CUP	ø12	ø12	ø13	38.6	ø15	ø18	4	2157344-1
FINISH	POLARIZATION	TERMINATION	A	Q	S	L	d	D	SHELL SIZE	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C THOMAS 06APR2012		
DIMENSIONS: mm		CHK R. GROSS 06APR2012		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. GROSS 06APR2012	NAME	
0 PLC ± -		PRODUCT SPEC	CIRCULAR HD PLUG WITH PIN CONTACTS 19 POS.	
1 PLC ± -		APPLICATION SPEC	-	
2 PLC ± 0.20		108-127005	SIZE	CAGE CODE
3 PLC ± -			A2	00779
4 PLC ± -			DRAWING NO	RESTRICTED TO
ANGLES ± 3°			C=2157344	-
MATERIAL		WEIGHT	SCALE	SHEET
5		-	NTS	1 of 1
FINISH		CUSTOMER DRAWING	SCALE	REV
6				C

1471-9 (3/11)

2157344

B

A