

623 Receptacle angled rotatable

speedtec

insulation insert uncoded housing code 1 flange mount /Flange 25x25

Technical Data

number of pins 12
temperature range -20 °C to 130 °C
protection type when connected IP 66/67
rotation range 330°

 Electrical Data
 signal

 rated current
 max. 7 A*

 rated voltage
 160 V (AC/DC)

 rated insulation voltage (L-L)
 2500 V

mating cycles 500

Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

pollution degree 3 over voltage category III max. height for operation 2000 m

Material

housing zinc diecast / chromated insulation insert PBT, UL 94 / V0 seals FKM

Contacts (not part of product contents)

Tools (not part of product contents)

A ED C 052 NN 00 00 1115 000 A G C 052 N 00 00 1115 000



Contact Arrangement mating view



© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH Bernrieder Straße 15 94559 Niederwinkling, Deutschland Tel.: +49 9962 2002-0 Fax: +49 9962 2002-70 E-Mail: intercontec@te.com Web: www.intercontec.biz



