


THIS DRAWING IS UNPUBLISHED.  
 VERTRAULICHE UNVEROEFFENTLICHTE ZEICHNUNG  
 © COPYRIGHT 2011

RELEASED FOR PUBLICATION  
 FREI FUER VEROEFFENTLICHUNG  
 - - 2011  
 ALL RIGHTS RESERVED.  
 ALLE RECHTE VORBEHALTEN.


LOC	DIST	REVISIONS AENDERUNGEN					
A1	-	P	LTR	DESCRIPTION BESCHREIBUNG	DATE	DWN	APVD
PROJEKT NR.:			A	NEW DRAWING	12DEC2011	VA	DWE
			A1	SEE BALLOON (A1)	23JAN2015	SMD	DWE



NOTES:  
 Bemerkungen:



- APPLICATION TEMPERATURE:  
 CONTINUOUS: -40 °C ... +125 °C  
 SHORT TERM: 60s max. 180 °C  
 Temperaturbereich:  
 Dauer: -40 °C ... +125 °C  
 kurzzeitig: 60s max. 180 °C
- DIMENSIONS TOLERANCE ACC. ISO 3601  
 Masstoleranzen in Anlehnung an ISO 3601

9-2177797-1	A	O-Ring, 3x1.5mm	SILIKON MVQ SHORE 50A	BLUE
<b>TE-PART-NO</b>	<b>REV</b>	<b>DESCRIPTION</b>	<b>MATERIAL</b>	<b>COLOUR</b>



DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT.  
 BEMASSUNGEN UND TOLERANZEN GEMAESS GPS (ISO STANDARDS).

THIS DRAWING IS A CONTROLLED DOCUMENT.  
 DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).

DIMENSIONS: MASSEINHEITEN: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN	DWN Vishwa A 12DEC2011	 TE Connectivity
	0 PLC ± - 1 PLC ± - DIN ISO 2 PLC ± - 2768-mK 3 PLC ± - 4 PLC ± - ANGLES/WINKEL ± -	CHK F.Wittrock 03JAN2012	
		APVD D.Weyrauch 04JAN2012	
MATERIAL SEE TABLE	FINISH/OBERFLAECHE/FARBE -	PRODUCT SPEC PRODUKTSPEZ. -	NAME O-Ring, 3x1.5mm
		APPLICATION SPEC VERARBEITUNGSSPEZ. -	SIZE A3
		WEIGHT GEWICHT 0.03g	CAGE CODE 00779
			DRAWING NO ZEICHNUNGS-NR. G= 2177797
			RESTRICTED TO NUR FUER -
		CUSTOMER DRAWING	SCALE MASSSTAB 10:1
		/KUNDENZEICHNUNG	SHEET BLATT 1 OF VON 1
			REV A1