

623 Receptacle angled rotatable

speedtec - ready

insulation insert uncoded housing code 1 flange mount /Flange 28x28 Anti-vibration o-ring

Technical Data

number of pins temperature range -20 °C to 130 °C protection type when connected IP 66/67 rotation range 330°

Electrical Data signal rated current max. 7 A* 160 V (AC/DC) rated voltage rated insulation voltage (L-L) 2500 V

mating cycles 500

Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

pollution degree 3 III over voltage category max. height for operation 2000 m

Material

housing insulation insert zinc diecast / chromated PBT, UL 94 / V0

Contacts (not part of product contents)

Tools (not part of product contents)

A ED C 052 NN 00 00 1200 000 A G C 052 N 00 00 1200 000



Contact Arrangement mating view



© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedted

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH Bernrieder Straße 15
94559 Niederwinkling, Deutschland
Tel.: +49 9962 2002-0
Fax: +49 9962 2002-70
E-Mail: intercontec@te.com
Web: www.intercontec.biz



