

## 917 Receptacle angled rotatable



insulation insert Code 3 male Connection Cross Section to 1.5 mm<sup>2</sup> Earth-to-Housing Connection according to VDE 0627 flange mount /Flange 21x21

## **Technical Data**

number of pins 4 (3+PE) power

temperature range protection type -20 °C to 130 °C

when connected IP 66/67

**Electrical Data** power signal max. 14 A\* 630V (AC/DC) max. 3.6 A\* 63 V (AC/DC) rated voltage rated insulation voltage (L-L) 6000 V 1500 V

mating cycles 500

## Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

pollution degree over voltage category max. height for operation 2000 m

## **Material**

zinc diecast / chromated housing insulation insert PBT, UL 94 / V0

seals

Contacts (not part of product contents)

Tools (not part of product contents)

B ED C 906 NN 00 00 051A 000 B G C 906 N 00 00 051A 000



**Contact Arrangement** mating view



© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedted

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH Bernrieder Straße 15
94559 Niederwinkling, Deutschland
Tel.: +49 9962 2002-0
Fax: +49 9962 2002-70
E-Mail: intercontec@te.com
Web: www.intercontec.biz



