








2213917-2 AS SHOWN



BUTTON 1

—BUTTON 2



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APV
	10	TE LOGO AND KEMA LOGO POSITION CHANGED	17SEP2018	RS	OL
	11	SHT 1: DIM (15.21) CHANGED TO (15.00)	19SEP2018	RS	OL
	12	NEW DESIGN	29AUG2019	RS	MG
	13	DRAWING UPDATE ACC. NEW DESIGN	18JUN2020	SD	MZ

NOTES:

1. CONNECTOR ACCEPTS MULTIPLE WIRES SIZES: SEE TABLE.
2. HOUSING AND BUTTON MATERIAL : POLYCARBONATE
3. IDC CONTACT MATERIAL: TIN PLATED, COPPER ALLOY.
4. LASER MARKING LOGO'S: KEMA, PARTNUMBER, UL, TE LOGO, DATE CODE, IP CLASS.
5. WIRE SIZE.
6. FOR WIRE INSULATION DIAMETER RANGE SEE DIMENSION "A" AND "B".


PRELIMINARY PART
NOT RELEASED FOR PRODUCTION

CONTACT ENGINEERING FOR LAST
REVISION BEFORE USING THIS DRAWING

Engineer: S. DERMISEK

A=3.00 B=3.00	GREEN	AWG22/20 (0.33/0.52mm2)	GREEN	AWG22/20 (0.33/0.52mm2)	SEALED	2213917-6	TBD
A=3.00 B=3.00	GREEN	AWG22/20 (0.33/0.52mm2)	GREEN	AWG22/20 (0.33/0.52mm2)	STANDARD	2213917-5	ON REQUEST
A=3.50 B=3.00	RED	AWG18/16 (0.75/1.5mm2)	GREEN	AWG22/20 (0.33/0.52mm2)	SEALED	2213917-4	YES
A=3.50 B=3.00	RED	AWG18/16 (0.75/1.5mm2)	GREEN	AWG22/20 (0.33/0.52mm2)	STANDARD	2213917-3	ON REQUEST
A=3.50 B=3.50	RED	AWG18/16 (0.75/1.5mm2)	RED	AWG18/16 (0.75/1.5mm2)	SEALED	2213917-2	YES
A=3.50 B=3.50	RED	AWG18/16 (0.75/1.5mm2)	RED	AWG18/16 (0.75/1.5mm2)	STANDARD	2213917-1	ON REQUEST
HOUSING WIRE ENTRY	COLOR	WIRE SIZE	COLOR	WIRE SIZE	DESCRIPTION	PART NUMBER	AVAILABLE
	BUTTON 1		BUTTON 2				

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±° 1 PLC ±° 2 PLC ±° 3 PLC ±° 4 PLC ±° ANGLES ±3°		P. POORTER APVD 20 JAN 2017 O. LEIJNSE		NAME COOLSPLICE 2 POSITIONS													
				PRODUCT SPEC 108-133061		SIZE CAGE CODE DRAWING NO RESTRICTED T A3 00779 C-2213917 -													
				APPLICATION SPEC 114-133061															
				WEIGHT -															
MATERIAL SEE NOTES		FINISH - -		CUSTOMER DRAWING						SCALE 2:1		SHEET 1		OF 2		REV 1		3	

