





TABLE OF DIMENSIONS												
PART	Н		J		Р	R	S	Т	U	JO	HW	JW
NUMBER	Min	Max	Min	Max	±10%	Ref	Ref	Ref	±10%	±10%	±20%	±20%
	а	b	а	b	b	b	b	b	b	b	b	b
0000001 05 /005	19.3	13.0	6.3	2.1	44.5	16.3	3.05	1.02	5.6	21.8	1.52	1.14
222D921-25/225	[.76]	[.51]	[.25]	[.08]	[1.75]	[.64]	[.12]	[.04]	[.22]	[.86]	[.06	[.045]
2220272 25 /225	26.1	19.1	7.6	2.6	67.3	18.0	3.05	1.02	8.4	29.2	1.78	1.14
222D932-25/225	[1.03]	[.75]	[.30]	[.10]	[2.65]	[.71]	[.12]	[.04]	[.33]	[1.15]	[.07]	[.045]
0000057 05 /005	34.2	26.0	9.6	3.0	81.3	18.8	3.05	1.02	11.4	36.3	1.78	1.14
222D953-25/225	[1.35]	[1.02]	[.38]	[.12]	[3.20]	[.74]	[.12]	[.04]	[.45]	[1.39]	[.07]	[.045]
222D963-25/225	43.6	34.1	11.4	3.6	115.6	21.3	3.05	1.65	15.5	47.0	1.78	1.14
2220903-25/225	[1.72]	[1.34]	[.45]	[.14]	[4.55]	[.84]	[.12]	[.065]	[.61]	[1.85]	[.07]	[.045]

ġ	nec		а	b	а	b	b	b	b	b	b	b	b	b		
DRAWING IS UNPUBL	Connec	222D921-25/225	19.3	13.0	6.3	2.1	44.5	16.3	3.05	1.02	5.6	21.8	1.52	1.14		
	믵		[.76]	[.51]	[.25]	[.08]	[1.75]	[.64]	[.12]	[.04]	[.22]	[.86]	[.06	[.045]		
		222D932-25/225	26.1	19.1	7.6	2.6	67.3	18.0	3.05	1.02	8.4	29.2	1.78	1.14		
	- 1		[1.03]	[.75]	[.30]	[.10]	[2.65]	[.71]	[.12]	[.04]	[.33]	[1.15]	[.07]	[.045]		
	됬	0000057 05 /005	34.2	26.0	9.6	3.0	81.3	18.8	3.05	1.02	11.4	36.3	1.78	1.14		
	YRIC	222D953-25/225	[1.35]	[1.02]	[.38]	[.12]	[3.20]	[.74]	[.12]	[.04]	[.45]	[1.39]	[.07]	[.045]		
	0	222D963-25/225	43.6	34.1	11.4	3.6	115.6	21.3	3.05	1.65	15.5	47.0	1.78	1.14		
			[1.72]	[1.34]	[.45]	[.14]	[4.55]	[.84]	[.12]	[.065]	[.61]	[1.85]	[.07]	[.045]		
DIMENSIONS: DWN 28JAN2019 MATERIAL FINISH											-					
		mm [INCHES]	PRA'	veen n	T			SEE S	SHEET 2				_			
	IIIII [INCHE3]		CHK N N	ACAR	28JAN	N2019										
		LERANCES UNLESS ERWISE SPECIFIED:	N NAGAR APVD 28JAN2019 TE Connectivity Ltd.													
	OTTENWISE STEETITED.		M T.	AYLOR												
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC		± -	PRODUCT SPEC NAME													
		± -	BOOT, 90 DEGREES, WITH LIP													
		± - ± -	APPLICATION SPEC —													
		± -	TAI I LICAI	HON SI LC		9	SIZE CAGE CODE DRAWING NO RESTRICTED TO									
ANG	LES	± -	-													
		\triangle	WEIGHT A4 00779 C- 222D9XX-25/225-0										_			
		Ψ	CUSTOMER DRAWING SCALE DNS SHEET 1 OF 2 REV [REV D			

REVISIONS