




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	REVISED PER ECR-23-169188	16MAR2023	MV	JP
	E1	REVISED PER ECR-23-175978	26MAY2023	MV	JP
	F	REVISED PER ECR-23-182036	08AUG2023	AK	JP
	F1	REVISED PER ECR-23-188860	09OCT2023	AK	JP

- 1 MATERIAL:
HOUSING- THERMOPLASTIC, UL94V-0, BLACK
CONTACT- COPPER ALLOY
CAVITY CARRIER TAPE- BLACK CONDUCTIVE PLOYCARBONATE
- 2 FINISH:
CONTACT - TIN PLATE FOR -2,-3,2--3,2--2,
GOLD PLATE FOR 1--2,1--3.1--4,
- 3 POSTS SOLDERTAILS MUST COMPLY WITH TE SOLDERABILITY SPEC 109-11-12.
- 4 HEADER ARE SUPPLIED ON A 330.2mm DIAMETER REEL WITH 225 PARTS PER REEL. THE CAVITY CARRIER TAPE HOLDS 1 PART PER POCCKET, ORIENTED AS SHOW.
- 5 PRIMARY REELING DIRECTION
- 6 REVERSE-REELING DIRECTION

6	972366-3	1706504-2	147117-5	2	3-647166-2	2-2232980-2
6	972366-4	1706504-4	147117-5	4	3-647167-4	1-2232980-4
6	972366-3	1706504-3	147117-5	3	3-647166-3	2-2232980-3
5	972366-3	1706504-3	147117-5	3	3-647167-3	1-2232980-3
5	972366-3	1706504-2	147117-5	2	3-647167-2	1-2232980-2
5	972366-3	1706504-3	147117-5	3	3-647166-3	2232980-3
5	972366-3	1706504-2	147117-5	2	3-647166-2	2232980-2
DIRECTION OF REELING	COVER TAPE	CARRIER TAPE	PICK AND PLACE CAP	NO. OF POSITIONS	HEADER ASSEMBLY	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN P.0 30JUN2015	TE Connectivity		
			CHK D.7 30JUN2015			
			APVD D.7 30JUN2015			
			PRODUCT SPEC			
DIMENSIONS: MM			108-1050	NAME MTA100 HDR ASSY SURFACE MOUNT, FRICTION LOCK, .025 SQUARE STRAIGHT POST		
			APPLICATION SPEC			
			114-1019	SIZE	CAGE CODE	DRAWING NO
MATERIAL 1			WEIGHT -	A200779	C-2232980	RESTRICTED TO -
			CUSTOMER DRAWING	SCALE 11:1	SHEET 1 OF 2	REV F1

D

D

C

C

B



B

A


A

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



CAP FOR HEADER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P.Q	30JUN2015		TE Connectivity					
		CHK D.Z	30JUN2015							
		APVD D.Z	30JUN2015							
DIMENSIONS: MM [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	MTA-100 HDR ASSEMBLY, SURFACE MOUNT, FRICTION LOCK, .025 SQUARE STRAIGHT POST					
		PRODUCT SPEC								
		108-1050								
		APPLICATION SPEC								
		114-1019		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
MATERIAL		FINISH		WEIGHT	A200779C=2232980			-		
				CUSTOMER DRAWING				SCALE 4:1	SHEET 2 OF 2	REV F 1