


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -
© COPYRIGHT copyright, dByte- ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	ECR-18-006054	26DEC2018	LZ	RR
	B	ECR-19-006634	12JUN2019	LZ	FL
	B1	ECR-21-112328	14SEP2021	SM	FL
	B2	ECR-22-129489	18FEB2022	PJ	FL









12 ALTERNATE LOCKING LATCH GEOMETRY (EXTENDED LOCKING LATCH)
FOR PN 5-2295787-5 AND 5-2295787-7





SCALE 2:1



POSITION OF KEYING RIB
AND THE LOCKING LATCH
OF THE HOUSING

NOTES

1. MATERIAL: PA66 UL94-V0 GWT750°C NF CTI 350V
2. POLARIZATION RIB GO THROUGH TO HINGE. POSITION "a" OR "b", AT CAVITY NO....
3. LOCKING DEVICE FOR COVER AT CAVITY NO
4. MATING STOP BETWEEN CAVITY NO 1 AND 2 ALSO BETWEEN THE LAST ONE AND LAST BUT ONE CAVITY
5. KEYING RIB POSITION "c" OR POSITION "d" AT CAVITY NO
6. LOCKING LATCH BETWEEN CAVITY NO
7. CONTACT CAVITY NO
8. AREA FOR TE LOGO
9. DIMENSION A AND DIMENSION B SEE TABLE
10. CAVITY MARKING
11. PRELIMINARY PART NUMBER
12. ALTERNATE LOCKING LATCH GEOMETRY
13. PRODUCT WITH HIGH RENTENTION FORCE EXCLUDING NOTE 15/LOCKING LATCH STANDARD VERSION: MORE SPACE FOR LATACH ENGAGEMENT ARE NEEDED IN COUNT PART SIDE. RECOMMEND SPACE: 4.0mm Min.
14. MATERIAL: PA66 UL-94 V0 & GWEPT 750°C NO FLAME ACCORDING TO IEC 60335-1
15. LOCKING LATCH STANDARD VERSION, SEE SHEET 2.
16. PART WITH LOW CLOSING FORCE OF TPA: MAX. 75N

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±0.2
1 PLC ±0.2
2 PLC ±0.2
3 PLC ±-
4 PLC ±-
ANGLES ±1°

MATERIAL 1

FINISH - -

DWN Shawn Li 12Mar2016
CHK Federico Lupo 20May2016
APVD Riccardo Robone 20May2016
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME STANDARD-TIMER HOUSING


SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-2295787	-

CUSTOMER DRAWING | SCALE 3:1 | SHEET 1 OF 2 | REV B2

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -
© COPYRIGHT copyright_dBYe- ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-


⚠15 SPECIAL LOCKING LATCH GEOMETRY (STANDARD VERSION) FOR PN 2-2295787-3



Other dimensions please refer to sheet 1

⚠16 ONLY FOR 7 POSITION PART






SCALE 2:1

Other dimensions please refer to sheet 1


⚠12 5-2295787-7	7	-	35	⚠1	NATURE
1-2295787-7	7	-	35		
2295787-7	7	07-C	35		
PART NO.	POS.	RAST 5	DIM A	MATERIAL	COLOUR

3pos
03-G




2295787-3

3pos




⚠15 ⚠11 2-2295787-3

4pos



⚠11 2295787-4


5pos
05-B



2295787-5


⚠12 5-2295787-5

7pos
07-C



⚠16 2295787-7

7pos



⚠16 1-2295787-7

⚠16 ⚠12 5-2295787-7

⚠12 5-2295787-5	5	05-B	25	⚠1	NATURE
2295787-5	5	05-B	25		
⚠11 2295787-4	4	-	20	⚠14	
⚠15 ⚠11 2-2295787-3	3	-	15		
2295787-3	3	03-G	15	⚠1	
PART NO.	POS.	RAST 5	DIM A	MATERIAL	COLOUR

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±0.2
1 PLC ±0.2
2 PLC ±0.2
3 PLC ±-
4 PLC ±-
ANGLES ±1°

MATERIAL

FINISH - -

DWN Shawn Li 12Mar2016
CHK Federico Lupo 20May2016
APVD Riccardo Robone 20May2016
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME STANDARD-TIMER HOUSING -

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-2295787	-

CUSTOMER DRAWING SCALE 3:1 SHEET 2 OF 2 REV B2

4805 (3/13)