
## **CUSTOMER DRAWING**



Product Name	Product Dimensions			Cable Dimensions			
AWG 22*	L±1.75	ØВ	ØС	ØD	ØΕ	ØF	ØG
	[L±0.07]	min	min	max	max	min	min
S02-07-R-90-65-T	16.5	2.65	3.68	3.68	2.65	1.40	0.75
	[0.650]	[0.105]	[0.145]	[0.145]	[0.105]	[0.055]	[0.030]
S02-08-R-90-65-T	16.5	4.30	5.08	5.08	4.30	2.15	1.25
302-08-R-90-03-1	[0.650]	[0.170]	[0.200]	[0.200]	[0.170]	[0.085]	[0.050]
S02-10-R-90-65-T	19.1	7.00	7.60	7.60	7.00	4.30	2.50
	[0.750]	[0.275]	[0.300]	[0.300]	[0.275]	[0.170]	[0.100]

## **MATERIALS**

- 1. INSULATION SLEEVE: Heat-shrinkable, transparent blue, radiation cross-linked polyvinylidene fluoride.
- 2. SOLDER PREFORM WITH FLUX AND THERMAL INDICATOR:

SOLDER: TYPE Sn63 per ANSI/J-STD-006.


FLUX: TYPE ROL1 per ANSI/J-STD-004.

THERMAL INDICATOR: Color change violet to colorless.

- 3. MELTABLE SEALING RINGS: Environment resistant thermoplastic. Color: blue.
- 4. PRE-INSTALLED LEAD: RAYCHEM 55A0111-22-90 IN ACCORDANCE WITH MIL-W-22759/32-22-90, with pretinned end. Color: white/black stripe.

## **APPLICATION**

- 1. These parts are designed to provide an environment resistant shield termination on cables, rated for 125°C minimum, meeting the dimensional criteria listed and having tin or silver-plated shields and insulation compatible with the insert material. For compatible insulations, consult TE Connectivity.
- 2. When installed per Raychem process standard RCPS-100-70, assemblies will meet those requirements of Raychem Specification RT-1404.
- 3. For assembly information, refer to TE Connectivity/Raychem document RCPS-100-70.
- 4. Parts shall be marked with identification code "S02XXR"; XX shall be replaced with the product size 07 thru 10.
- 5. For best results, prepare the cable as shown:



= TE				Raychem DEVICES	SOLDERSLEEVE SHIELD TERMINATOR ENVIRONMENT RESISTANT WITH PRE-TINNED END LEAD				
Unless otherwise s [Inches dimensions				eters.	DOCUMENT NO.:	S02-X	X-R-90-6	5-T	
TOLERANCES:	ANGLE	ES: N/A		nectivity reserves the right to					
0.00 N/A 0.0 N/A 0 N/A	ROUGI MICRO	HNESS IN	should e	his drawing at any time. Users valuate the suitability of the for their application.	REV: D1		DATE: 27OCT2023		
PREPARED BY: D. MALLII	KA	CAGE 0		ECN: ECN-23-234831	SCALE: NTS		SIZE:	SHEET: 1 of 1	

© 2022 TE Connectivity Ltd. Family of Companies. All Rights Reserved.

<sup>\*</sup>TE Connectivity, TE connectivity (logo), Raychem, Thermofit, SolderSleeve are trademarks

## **CUSTOMER DRAWING**

Unless otherwise specified dimensions are in millimeters. (Inches dimensions are shown in brackets)

()							
DOCUMENT NO.:	REV:	ECO NUMBER:	DATE:	SHEET:			
D-150-0253	A	XXXX	30-May-03	2 of 2			

Print Date: 27-Oct-23 If this document is printed it becomes uncontrolled. Check with the web for the latest revision