





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
1		PRELIMINARY RELEASE	03MAY2016	JW SH
2		CHANGE LENGTH TO 35MM	10MAY2016	JW SH



NOTES:

- UNLESS OTHERWISE SPECIFIED
- 1 MATERIAL: 6063 ALUMINUM.
- 2 FINISH: ELECTROLESS NICKEL, 0.76-2.54 MICROMETERS THICK. RoHS COMPLIANT.
- 3. 0,2mm MAX BURR.
- 4. VARIATION IN PLATING COLOR IS NORMAL AND ALLOWED.
- 5 MAXIMUM PIN LEAN OF 8° IN ANY DIRECTION.
- 6. RoHS COMPLIANT AND CERTIFIED.

DESIGN APPROVED THIS PRINT IS
PRELIMINARY
 TO FIRST PIECE APPROVAL
 CONTACT PRODUCT ENGINEERING
 BEFORE USING THIS PRINT

2	2303922-2
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. WANG 03MAY2016	TE Connectivity	
DIMENSIONS: mm		CHK S. HAN 03MAY2016		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. HAN 03MAY2016	NAME HEAT SINK SFP DWDM 4.2mm TALL	
0 PLC ±-		PRODUCT SPEC -	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
1 PLC ±.2		APPLICATION SPEC -	A20779 C-2303922	
2 PLC ±.10		WEIGHT -	SCALE 4.000 SHEET 1 OF 1 REV 2	
3 PLC ±.08		CUSTOMER DRAWING		
4 PLC ±0.0001				
ANGLES ±5				
FINISH 2				