




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW RELEASE	08APR2021	MK	BC




2320926-2
SCALE 2:1
KEY B




2320926-3
SCALE 2:1
KEY C



2320926-4
SCALE 2:1
KEY D



- COMPANY LOGO
- SCALE 2:1
- 1 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: GRAY
- 2 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: (SEE TABLE)
- 3 MATERIAL: SILICONE
COLOR: LT GRAY.
4. RECOMMENDED WIRE DIAMETER RANGE IS 1.30 TO 2.54mm.
5. RECOMMENDED BACKSHELLS:
- STRAIGHT EXIT
- A. 2292860-1 SMOOTH WIRE EXIT
- B. 2292860-2 NC12/NW10 CONDUIT WIRE EXIT
- C. 2292860-3 NC08/NW7.5 CONDUIT WIRE EXIT
- 90° EXIT
- D. 2302481-1 SMOOTH WIRE EXIT
- E. 2302481-2 NC12/NW10 CONDUIT WIRE EXIT
- F. 2302481-3 NC08/NW7.5 CONDUIT WIRE EXIT
6. RECOMMENDED SEAL PLUG: 776363-1.
7. MATING CONNECTOR: 2320932-X.



ORANGE	2320926-4
PURPLE	2320926-3
BLUE	2320926-2
TAN	2320926-1
TPA COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. MCNEAL 09OCT2017	TE Connectivity		
DIMENSIONS: mm		CHK R. BALTER 09OCT2017			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. BALTER 09OCT2017	NAME CAP ASSEMBLY, 2 POSITION, REDUCED DIA SEAL, HIGH TEMP, AMPSEAL 16		
0 PLC ± 1 PLC ± 2 PLC ±0.30 3 PLC ± 4 PLC ± ANGLES ± FINISH		PRODUCT SPEC 108-32602 APPLICATION SPEC 114-32362 WEIGHT 9g	SIZE A200779	CAGE CODE C-2320926	RESTRICTED TO -
MATERIAL -		CUSTOMER DRAWING	SCALE 4:1	SHEET OF	REV A