


4

3

2

1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H	REV PER ECO 20-002238	7-21-20	CT	PD



BODY: COPPER ASTM-B187 ANNEALED
TIN PLATE .00381[.000150] MIN THICK
PER MIL-T-10727

INSERT & FUNNEL: BRASS ASTM B36
NICKEL PLATE SAE AMS QQ-N-290A,
DATED JULY 2000,.00254 [.000100] MIN
THICK

1. WIRE INSULATOR : 10.8[.425] TO 11.9[.469]
2. WIRE CMA: 83700 TO 119500
3. THE TONGUE RADIUS FEATURE IS NOT A TOOLING CONTROLLED DIMENSION AND MAY NOT BE A TRUE RADIUS
4. WEIGHT: 55 GRAMS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G.ROBERT MAI 89	 TE Connectivity		
		CHK G.ROBERT 16-JAN-97			
		APVD G.ROBERT 16-JAN-97	NAME SEALED COPALUM		
		PRODUCT SPEC			
		APPLICATION SPEC			
		WEIGHT 0.000000	SIZE A3	CAGE CODE 00779	DRAWING NO C-134593
		CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 1
				REV H	