



REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-	-	-	-	-

### SPECIFICATIONS

- INPUT VOLTAGE : 3.0 Vrms (NOM)
- INPUT FREQUENCY : 2.5 kHz (NOM)
- ELECTRICAL STROKE : ± 5.000 INCHES [127]
- SENSITIVITY : .108 mV/VOLT/.001 INCH NOM.
- SENSITIVITY : 4.25 mV/VOLT/mm NOM
- NON-LINEARITY : 0.25% OF FULL RANGE (MAX)
- PHASE SHIFT : +0°
- IMPEDANCE
- PRIMARY : 480 OHM (NOM)
- SECONDARY : 470 OHM (NOM)

REV.	DESCRIPTION	DATE:	APPR.
A	UPDATED ELECTRICAL NULL POSITION	3/11/96	R.E.A.
B	UPDATED SENSITIVITY / REFORMAT SPECS PER ECN 1062	1/28/08	MFG/AG



[ ] DENOTES MILLIMETERS.

⊙ DENOTES CENTER OF CORE AT ELECTRICAL MID POINT.

<small>UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES          TOLERANCES ARE:          ANGLES: ± 0.5 DEG.          DECIMAL: XX= +/- .01          .XXX= +/- .005</small>	DRAFTSMAN: R.E.A.	DATE: 8 JUL 95	<b>Macro Sensors</b> Div. of Howard A. Schaevitz Technologies, Inc.	
	CHECKER:	DATE:		
	APPROVED:	DATE:	TITLE <b>OUTLINE</b> <b>HSA 750 5000</b>	
	APPROVED:	DATE:	C.A.G.E. No. <b>A 06WW0</b>	DRAWING No. <b>010914090000</b>
FINISH:	APPROVED:	DATE:	SCALE: NONE	SHEET No. 1 of 1

This Drawing and Specifications are the property of Macro Sensors, Div. of Howard A. Schaevitz Technologies, Inc. DO NOT COPY without the written approval of Macro Sensors.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
INCHES	
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
	ANGLES ± -
MATERIAL	FINISH
-	-

DWN	-		NAME			
CHK	-		OUTLINE HSA 750 5000			
APVD	-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
PRODUCT SPEC	-		A2	00779	C=010914090000	-
APPLICATION SPEC	-	CUSTOMER DRAWING		SCALE	SHEET	REV
				NTS	1 of 1	B