


REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-	-	-	-	-

SPECIFICATIONS

INPUT VOLTAGE: 18.0
 INPUT FREQUENCY: 2.4 KHz
 ELECTRICAL STROKE: +/- 0.100" [2.54]
 SENSITIVITY: 3.3 mv / VOLT / .001"
 SENSITIVITY: 84.7 mv / VOLT / mm
 NULL VOLTAGE: .035 VOLTS rms MAXIMUM
 LINEARITY: 0.50% OF FULL RANGE
 PHASE SHIFT: 0 DEGREES @ 2.4 KHz
 PRIMARY IMPEDANCE: 105 OHMS
 SECONDARY IMPEDANCE: 195 OHMS
 PER OWENS BROCKWAY PART NO. GAC-3901

REVISIONS

REV.	DESCRIPTION:	DATE:	APPR.
A	ADDED OWENS BROCKWAY PART NO GAC-3901 TO SPECIFICATIONS	1/23/97	R.E.A
B	ADDED NULL VOLTAGE, REMOVED SIN XXXX	3/13/97	R.E.A
C	00.3124/.003 WAS 00.311+/- .003	1/29/98	R.E.A



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES. TOLERANCES: ANGLES: +/- .5 DEGR. FRACTION: +/- 1/64 DECIMAL: .XX +/- .01 .XXX +/- .005	DRAFTSMAN: R.E.A.	DATE: 8 DEC 95	Macro Sensors Div. of Howard A. Schaevitz Technologies, Inc.		
	CHECKER:	DATE:			TITLE PR 750 101-0107 OUTLINE
	APPROVED:	DATE:	A	C.A.G.E. No. 06WW0	DRAWING NO. 015912511000
	APPROVED:	DATE:	SCALE: NONE		SHEET 1 OF 1

MATERIAL:

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	-		TE Connectivity		
DIMENSIONS: INCHES		CHK	-		NAME PR 750 101-0107 OUTLINE		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD	-		DRAWING NO. 015912511000		
MATERIAL		FINISH	-		SIZE A2	CAGE CODE 00779	RESTRICTED TO -
CUSTOMER DRAWING				SCALE NTS	SHEET 1 OF 1	REV C	