



© COPYRIGHT 1981, 83 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS						
P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
			O	RELEASED		
			O	ADDED 3-.8, 4-.0, 4-1. ECN 4143	12-09-81	MS
			D2	REV. ECN 4837	06-29-82	SO
			A	REV. ECN 253	06-25-84	MS
			A1	REV. ECN 1596	07-27	MS
			B	REV. ECN AN 2515	07-25-84	BS
			C	REV LOC & DIST AD-4171	11-28-89	BF
			D	REV PER 0010-1406-93 TT	10-22-93	JK
			E	REV PER 0010-0688-94	06-10-94	JK



- △ APPLICATOR CUT-OFF DIMENSION.
- △ .000100-.000200 BRIGHT TIN-LEAD OVER .000050 NICKEL.
- △ .000030 GOLD OVER .000050 NICKEL.
- △ .000015 GOLD OVER .000050 NICKEL.
- △ .000050 GOLD OVER .000050 NICKEL.
- △ POINT OF MEASUREMENT FOR PLATING THICKNESS.
- △ .000030 GOLD IN THE CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON THE SOLDER TAIL, ALL OVER .000050 NICKEL
- △ POST THICKNESS PERMITTED TO BE .0270 MAX IN THIS AREA AFTER STAMPING

OBSOLETE	7	1.238	.960	.278	4-102830-2
	5	1.238	.960	.278	4-102830-1
	3	1.390	1.160	.230	4- -0
	3	1.190	.960	.230	3- -8
	3	1.016	.738	.278	3- -6
	4	.815	.255	.560	2- -4
	4	.625	.350	.278	2- -3
	3	.393	.715		2- -0
	5	1.478	1.200		2- -5
	2	1.016	.738		2- -6
OBSOLETE	2	1.435	1.160		2- -5
	2	1.238	.960		2- -4
OBSOLETE	4	1.016	.738		2- -3
	4	.863	.575		2- -2
OBSOLETE	4	1.053	.775		2- -1
	3	1.438	1.160		2- -0
OBSOLETE	4	1.438	1.160		1- -9
	3	1.238	.960		1- -8
OBSOLETE	4	1.238	.960		1- -7
	4	.925	.650		1- -6
	4	.728	.450		1- -5
	4	.878	.550	.278	1-02830-4

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.005 ANGLES	CONTRACT NO 10-12-81	AMP INCORPORATED Harrisburg, Pa.
	MATERIAL PHOS BRONZE	
FINISH SEE TABLE	OTHER APPD	SIZE CODE IDENT NO DRAWING NO C 00779 102830
SCALE N.T.S.		SHEET 1 OF 1