

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	PRODUCTION ISSUE	30JAN2019	PNT	MT





TABLE OF DIMENSIONS


PART NUMBER	H		J		K		P	R	S	U	HY	HW	JO	JW	KO	KW	C°
	Min	Max	Min	Max	Min	Max	±10%	Ref	Ref	Ref	±10%	±20%	±20%	±20%	±20%	±20%	REF
	a	b	a	b	a	b	b	b	b	b	b	b	b	b	b	b	a
322W204	26.0 [1.02]	6.3 [.25]	18.0 [.71]	5.3 [.21]	18.0 [.71]	5.3 [.21]	90.0 [3.54]	35.0 [1.38]	5.0 [.20]	54.0 [2.13]	5.5 [.22]	2.5 [.10]	11.0 [.43]	2.0 [.08]	11.0 [.43]	2.0 [.08]	30

DIMENSIONS:

mm [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± 0.50 [.10]
2 PLC	± 0.25 [.01]
3 PLC	± 0.13 [.005]
4 PLC	± -
ANGLES	± 5°



DWN 30JAN2019

PRAVEEN N T

CHK 30JAN2019

N NAGAR

APVD 30JAN2019

M TAYLOR

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

MATERIAL

SEE SHEET 2

FINISH

—



TE Connectivity Ltd.

NAME

TRANSITION, 90 DEGREE, SIDE BREAKOUT

SIZE

A4

CAGE CODE

00779

DRAWING NO

C-322W204-XX-0

RESTRICTED TO

—

CUSTOMER DRAWING

SCALE

DNS

SHEET

1 OF 2

REV

F

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

COPYRIGHT - TE Connectivity Ltd.

COMPATABILITY CHART				
MATERIAL DASH NO.	MATERIAL DESCRIPTION	RT SPEC	COATING SLASH NO.	COATING S NO.
-25	Elastomer, Fluid Resistant	RW-2070	/42; /86; /225	S1017; S1048; S1206

322W204 -XX /XX -0

Base part number _____

Material dash number _____
(See Compatibility Chart)

Adhesive slash number _____
(If necessary, see Compatibility Chart)

Color Designator _____

1. Dimensions appearing in table are as follows:
 - a - As Supplied
 - b - After Unrestricted Recovery
- 2.. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by 1.5mm[.06] max.

1469-35 (1/15)