


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
--	REVISED	9/8/94	BB
01 <sub>3</sub>	REVISED PER ECN 99-0001	DM 5/19/99	PCW 7/14/99



OUTLINE, -50 AND B/M MUST CARRY THE SAME REVISION LEVEL

OUTER CONTACT	BERYLLIUM COPPER	GOLD PLATE OVER NICKEL PLATE
CENTER CONTACT	BERYLLIUM COPPER	GOLD PLATE OVER NICKEL PLATE
DIELECTRIC	POLYPROPYLENE, GF	N/A
CABLE JACKET	FLUORINATED ETHYLENE-PROPYLENE	N/A
SHIELD	SILVER COATED COPPER WIRE, 38 AWG	N/A
DIELECTRIC	PERFLUOROALKOXY OR POLYTETRAFLUOROETHYLENE	N/A
CENTER CONDUCTOR	SILVER COATED COPPER CLAD STEEL	N/A

COMPONENT	MATERIAL	FINISH
-----------	----------	--------

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON FRAC DEC ANGLES ± 1/64 ± .005 ± 1°	DRAWN BY <i>BB</i> DATE 10/9/92	AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599
	CHECKED BY	
	APPD BY <i>J.Davis</i> 10/12/92	<b>AMP</b>

These drawings and specifications are the property of AMP Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASSY PROCEDURE	TITLE OSMT RIGHT ANGLE JACK CABLE PIGTAIL, HIGH TEMPERATURE	
	NO. A.P. <u>N/A</u>	SIZE B	CODE IDENT NO. 26805
		SCALE 10:1	9952-2305-23
			SHEET 1 OF 1

ELECTRICAL

Frequency DC - 6 GHz  
 Nominal Impedance 50 ohms  
 Voltage Rating 250 Volts (VRMS Max.) @ Sea Level  
 VSWR 1.20:1 Max. @ 2GHz  
 1.40:1 Max. @ 6GHz  
 Insulation Resistance 1000 Megohms Minimum  
 Dielectric Withstanding Voltage 500 Volts (VRMS Minimum) @ Sea Level

MECHANICAL

Connector Durability 100 mating cycles

ENVIRONMENTAL

Temperature Rating -55°C (-67°F) To +150°C (302°F)