





P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-


"A" DIA FOR "B" STUD
SEE TABLE




1 WIRE INSULATION: 10.8[.425]-.11.9[.469]

2 WIRE CMA: 83700 to 119500

3 THE TONGUE RADIUS FEATURE IS NOT A TOOLING CONTROLLED DIMENSION AND MAY NOT BE A TRUE RADIUS.



57 GRAMS	6.73±0.13 [.265±.005]	1/4 or M6	BODY: COPPER ASTM B187 ANNEALED TIN PLATE .00381[.000150] MIN THICK PER MIL-T-10727	134452-3
56 GRAMS	8.34±0.13 [.328±.005]	5/16 or M8	INSERT&FUNNEL:BRASS ASTM B36 NICKEL PLATE SAE AMS QQ-N-290A, DATED JULY 2000..00254 [.000100] MIN THICK	134452-2
WEIGHT	DIM A	B	MATERIAL&FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JJ. DESPRETZ 23JUN2004	 TE Connectivity					
DIMENSIONS: mm[Inches]		CHK G-ROBERT 23JUN2004						
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.3 1 PLC ±0.3 2 PLC ±0.13 3 PLC ±.1 4 PLC ±.1 ANGLES ±.5	APVD Y. PETRONIN 23JUN2004	NAME SEALED COPALUM ASSEMBLY, 1/0, ALU -					
		PRODUCT SPEC -						
	MATERIAL TABLE -	APPLICATION SPEC -	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
		WEIGHT -	A3	-	C-134452			
CUSTOMER DRAWING			SCALE	2:1	SHEET	2 OF 2	REV	M