



CUSTOMER DRAWING

DRAWING NUMBER - 466449 SHEET 2 OF 2 REV. H1

2	-	5-354779-8	PIN, WIRE DISC, .3280	128
2	-	4-354779-6	PIN, WIRE DISC, .3220	127
2	-	4-354779-0	PIN, WIRE DISC, .3190	126
-	-	21055-5 455749-1	WASHER, FLAT, REG NO 6 GUARD WINDOW	119
-		679532-1	INSERT, GUARD	115
		690603-1	SPRING ASSIST AMP-O-MATOR APPLICATOR	112
İ	-	1-21002-7	SCR, BTN SKT HD CAP 6-32 X .375	91
	-	3 8563-	GUARD, FRONT CHIP	89
	-	240641-5	SPACER	81
	-	4088040	SF APPL INST 408-8040	72
	-	217238-1	GENERAL INSTRUCTION PKG	171
	-	46 264-	PLATE, IDENTIFICATION	67
2	-	21017-2	SCREW, DRIVE	66
	-	<u>986950-1</u> 21009-2	WASHER, FLAT PRECISION	64
	-	23030-1	SCR, SET, SELF LOCKING 1/4-20 X .250 SCR, SKT HD CAP 6-32 X .25	62
1	-	22733-8	SCR, BHSC, SELF-LOCKING, 8-32 X .375	160
1	-	2-22603-0	SCR, HEX HD CAP 8-32 X .312	59
İ	-	458537-2	PAWL, FEED	56
4	-	2-21002-2	SCR, BTN SKT HD CAP 8-32 X .500	54
2	-	2-2 000-8	SCR, SKT HD CAP 8-32 X .625	53
-		690602-6	CAM, PRE FEED, I 5/8	49 (
-		690602-5	CAM, PRE FEED, I I/8	48
1	-	690501-4	CAM, POST-FEED I 5/8	47
	-	459456-1	APPL. BASIC SUB ASSY (SIDE WISE MQCA)	46
<u> </u>	-	<u>690 9 - </u> 455673-	PLUG,NYLON RAM. SIDE FEED	45
 	-	690125-1	RAM, SIDE FEED SHIM SUB-ASSY	44
1	-	690124-1	WASHER, RAM (.115)	43
	-	7-21002-9	SCR, BTN SKT HD CAP 5/16-24 X 1.00	4
	-	23241-6	BALL, STEEL	40
	-	690170-1	SPRING, COMPRESSION	39
	-	690 42-	DISC, INSULATION	38
	-	354777-1	WIRE DISC, ASSEMBLY	37
	-	22480-5	SPRING, COMPRESSION	36
<u> </u>	-	690212-1	POST, RAM	35
2	-	2-21002-4	SCR, BTN SKT HD CAP 8-32 X .750	33
	-	21024-5 3-21000-4	WASHER, SPRG LOCK, REG NO IO SCR, SKT HD CAP IO-32 X .375	32
1	-	1-1320908-7	SPACER, STRIP GUIDE	30
1	-	1633091-1	ASSEMBLY, STRIP GUIDE	29
İ	-	1-455888-0	SPACER, CRIMPER	28
1	-	320928 -	PLATE, STRIP GUIDE	24
	-	690472-2	STRIPPER	22
	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500	21
4	-	21024-4	WASHER, SPRG LOCK, REG NO 8	20
-	-	691353-1	STRIPPER	19
	-	690518-2	HOLD DOWN, TERMINAL	18
2	-	690463-1	FLOATING SHEAR, REAR SCR, SKT HD CAP 6-32 X .250	117
<u> </u>		<u> -2 000-8</u> 690464-2	SHEAR PLATE, REAR	16
	-	690462-1	SHEAR HOLDER, REAR	14
-	-	679625-1	SHEAR HOLDER, FRONT (NO CUT)	13
2	-	3-22280-3	SPRING, COMPRESSION	12
2	-	690461-1	STOP, SHEAR	
	-	690459-1	SHEAR HOLDER, FRONT	10
	-	454276-1	FLOATING SHEAR, FRONT	9
	-	690512-9	ANVIL, COMBINATION	8
-		-		7
<u> </u>	-	690468-1	DEPRESSOR SHEAR, REAR	6
	-	455889-9	DEPRESSOR, SHEAR	5
	-	2-238011-2 4-456135-4	BLOCK, CRIMPER SPACER CRIMPER, INSULATION O PREMIUM	4
	-	455888-5	SPACER, CRIMPER	2
1	-	1-456402-4	CRIMPER. WIRE PREMIUM	·
	U7.M		DESCRIPTION	ITEM ,
		PART NO	FC2000	NO '
ENĞÎÑĚĖ EST REVIS	CNICS CORF ING ORBANI ION.	Y, YIN CHK I 9D	ÉC2008 EC2008 ₹Tyco Electronics Harrisburg, PA 17105-3608	
ERANC	ES UNLE: SPECIFI	M. HEKK	FC2008 NAME	
SRWISE		PRODUCT SPEC	SIDE FEED HDM APPLICATOR	
±		1	-	
± ±	- 0.1 0.01	-		
± ±	- 0.1 0.01 0.001 0.0001 +	- APPLICATION SPEC	SIZE CAGE CODE DRAWING NO RESTR	ICTED TO
± ±	3 01	APPLICATION SPEC	A 00779 C= 466449	-
± ±	3 01	-	A 00779 C= 466449	істер то - ^{ev} Н

	2			1			
LOC	DIST			REVISIONS			
А	66	P	LTR	DESCRIPTION	DATE	DWN	APVD
			1	DEVELOPMENT	15DEC2008	Υ.Υ	D.N
			Н	RELEASED	08JAN2009	MEH	TE