










LOC	DIST	REVISIONS				
P	LYR	DESCRIPTION	DATE	OWN	APVD	
G		ECR-09-004948	11MAR2009	JS	JH	
H		ECR-09-011177	08JUN2009	JS	JH	
J		ECR-10-013382	28JUN2010	JS	DB	





CERTIFICATION: UL/CUL FILE NO. E102980 HZ. V.A.
 DIMENSIONS FOR REFERENCE ONLY. 50/60 2.4

PRIMARY	SECONDARY		P.U. PART NUMBER	TYCO ELECTRONICS PART NUMBER
	SERIES	PARALLEL		
115 VAC	10 VCT	5 VAC	4900-8010RB6I	2-1672209-4
115 VAC	12.6 VCT	6.3 VAC	4900-8013RB6I	2-1672209-6
115 VAC	16 VCT	8 VAC	4900-8016RB6I	2-1672209-7
115 VAC	20 VCT	10 VAC	4900-8020RB6I	2-1672209-8
115 VAC	24 VCT	12 VAC	4900-8024RB6I	2-1672209-9
115 VAC	120 VCT	60 VAC	4900-8120RB6I	3-1672209-5
115/230 VAC	10 VCT	5 VAC	4900-9010RB6I	1-1672209-0
115/230 VAC	12.6 VCT	6.3 VAC	4900-9013RB6I	1-1672209-1
115/230 VAC	16 VCT	8 VAC	4900-9016RB6I	1672209-9
115/230 VAC	20 VCT	10 VAC	4900-9020RB6I	1-1672209-6
115/230 VAC	24 VCT	12 VAC	4900-9024RB6I	1-1672209-7
115/230 VAC	120 VCT	60 VAC	4900-9120RB6I	2-1672209-3



SAMPLE LABEL
 SCALE: 6:1

VOLTAGE ON LABEL WILL VARY PER MODEL NUMBER



DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		OWN		Tyco Electronics	
INCHES [mm]				CHK	DATE	NAME	Harrisburg, PA 17105-3608
0 PLC	±	0 PLC	±	SLIKE	17AUG2007		
1 PLC	±	1 PLC	±	HAGGARD	17AUG2007		
2 PLC	±.01	2 PLC	±	APVD	17AUG2007		
3 PLC	±.005	3 PLC	±	HURLBERT			
4 PLC	±	4 PLC	±				
ANGLES		PRODUCT SPEC					
FINISH		APPLICATION SPEC					
		WEIGHT					
		SIZE					
		CAGE CODE					
		DRAWING NO					
		RESTRICTED TO					
		A200779					
		C=4900-RB61					
		CUSTOMER DRAWING					
		SCALE					
		3:2					
		SHEET					
		1					
		OF					
		REV					
		J					