




LOC	DIST	REVISIONS					
F	7	P	LTR	DESCRIPTION	DATE	DWN	APVD
			P	REVISED PER ECO-11-005150	21MAR11	RK	HMR


- 1 SENS DE BOBINAGE STANDARD (POUR APPLICATEUR STANDARD).
- 2 SENS DE BOBINAGE INVERSE (POUR MINI-APPLICATEUR).



CONTACT EN VRAC



					DIMENS. FIL VOIR CI-DESSUS		ISOLANT -	
28-32	0.5-1.0	DORE 0.8µM DANS LA ZONE DE CONTACT FLASH D'OR SUR LE RESTE SOUS-COUCHE 1.27µM NI.	11.7	0-167023-2		0-167020-2		
						-		
28-32	0.5-1.0	DORE 0.8µM DANS LA ZONE DE CONTACT ETAIN SUR LE FUT SOUS-COUCHE 1.27µM NI.	11.7	0-167023-1		0-167020-1		
						-		
20-26 (0.5mm ² MAX)	1.40 MAX	DORE 0.8µM DANS LA ZONE DE CONTACT ETAIN SUR LE FUT SOUS-COUCHE 1.27µM NI.	12.3	0-141603-4		0-167300-8		
						0-167300-7		
20-26 (0.5mm ² MAX)	1.40 MAX	DORE 0.8µM DANS LA ZONE DE CONTACT FLASH D'OR SUR LE RESTE SOUS-COUCHE 1.27µM NI.	12.3	0-141603-3		0-167300-6		
						0-167300-5		
JAUGE AWG FIL	DIAMETRE ISOLANT (MM)	FINITION	DIM 'A'	REFERENCE CONTACT EN VRAC	REFERENCE CONTACT EN BANDE			

DIMENSIONS:		DWN	20.MAR.89		MATERIAL		FINISH				
mm		A.CAMEL		BRONZE PHOSPHOREUX		VOIR CI-DESSUS					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	—		 TE Connectivity						
		APVD	—								
		PRODUCT SPEC		NAME							
		—									
		APPLICATION SPEC									
0 PLC ± —		—		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO			
1 PLC ± 0.3		—		A4		00779	C-141603	—			
2 PLC ± —		—									
3 PLC ± —		—									
4 PLC ± —		—									
ANGLES ± 5°		WEIGHT		—							
		CUSTOMER DRAWING				SCALE	5:1	SHEET	1 OF 1	REV	P