


DRAWING MADE IN THIRD ANGLE PROJECTION

1. LABEL TO BE MARKED WITH AMP P/N
CUSTOMER P/N, DATE CODE, AND
MANUFACTURE LOCATION AS FOLLOWS:

158017-1
44553-01
ASSEMBLED IN
MEXICO YYWW



PIN #	COLOR	LENGTH
1	YELLOW (6)	4.50
2	GRAY (7)	4.50
3	BLUE (8)	4.50
4	VIOLET (9)	4.50
5	WHITE (10)	4.50
6	BROWN (11)	4.50
7	ORANGE (12)	4.50
8	GREEN (13)	4.50
9	RED (14)	4.50
10	BLACK (2)	4.50

4.50	IN	A	992112-2	26 AWG HOOK-UP WIRE, RED	14
4.50	IN	A	992112-6	26 AWG HOOK-UP WIRE, GREEN	13
4.50	IN	A	992112-7	26 AWG HOOK-UP WIRE, ORANGE	12
4.50	IN	A	992112-8	26 AWG HOOK-UP WIRE, BROWN	11
4.50	IN	A	992112-3	26 AWG HOOK-UP WIRE, WHITE	10
4.50	IN	A	992112-5	26 AWG HOOK-UP WIRE, VIOLET	9
4.50	IN	A	1-992112-0	26 AWG HOOK-UP WIRE, BLUE	8
4.50	IN	A	992112-4	26 AWG HOOK-UP WIRE, GRAY	7
4.50	IN	A	1-992112-1	26 AWG HOOK-UP WIRE, YELLOW	6
1	-	C	3-173983-0	CT RECEPT. CONN. 10 POS. IDC	5
1	-	A	982293-5	LABEL	4
1	-	A	1-992114-5	3.00" GRAYLINE TUBING	3
4.50	IN	A	992112-1	26 AWG HOOK-UP WIRE, BLACK	2
1	-	C	1-173977-0	CT RECEPT. CONN. 10 POS. IDC	1

QTY REQD PER ASSY	U/M	DWG SIZE	PART NO	DESCRIPTION	ITEM NO
-1	U/M		158017.8.11	DESCRIPTION	

REV	DATE	BY	CHKD	DESCRIPTION
B	8/3/93	HK	HK	CHGD PER ECN 0420-0330-93
A	8/5/93	HK	HK	CHGD PER ECN 0420-0271-93
P				LTR REVISION RECORD

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION . 19

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

DO NOT SCALE PRINT.

UNLESS SPECIFIED DIMENSIONS IN (INCHES)

TOLERANCES ON:
2 PLC DEC ± .25
3 PLC DEC ± -
ANGLES ± -

LOC EV DIST 71

DR 7/2/93
H KANDOLF

CHK 8/6/93
C STEWART

APPD 8/6/93
R BRENNAN

APPD 8/6/93
H KANDOLF

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

AMP AMP Incorporated
Harrisburg, PA 17105-3608

NAME
CABLE ASSY., 10 WIRE, DOUBLE ENDED

SIZE CAGE CODE DRAWING NO
00779 C-158017

SCALE NTS SHEET 1 of 1 REV B