




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
D6		REVISED PER ECR-19-007141	3SEP2019	JH PKS

- SPECIFICATIONS:
MAGNET WIRE #18-#34 AWG. 0.16-1.02 [.006-.040] DIA COPPER. OTHER SIZES MAY BE ACCOMMODATED, CONSULT TYCO ELECTRONICS FOR APPROVAL.
- POCKET RECOMMENDATION: #1601425.
ALTERNATE POCKET #1601421.
- NOTES: TERMINALS SUPPLIED ON REELS, CAN BE SUPPLIED LOOSE PIECE.
- COATED OVERALL WITH VARNISH RESIST WHEN INDICATED IN TABLE BELOW.
- TERMINAL TO BE APPLIED PER TYCO ELECTRONICS SPECIFICATION 114-13166 FIGURE 7.
- TWO(2) TERMINALS SHOWN FOR ILLUSTRATION PURPOSES ONLY.
- PRE-PRODUCTION - F.A.S.R REQUIRED



OBSOLETE

OBSOLETE

PRE TIN PLATE	-	4-1601005-2																												
UNPLATED	-	4-1601005-1																												
UNPLATED \triangle_4	-	1601005-3																												
PRE TIN PLATE	131-012-002	1601005-2																												
UNPLATED	131-012-000	1601005-1																												
FINISH	REFERENCE PART NUMBER	TE PART NUMBER																												
THIS DRAWING IS A CONTROLLED DOCUMENT. DWN J.WELLER 11JAN2002 CHK M.FEHER 11JAN2002 APVD K.RANDOLPH 11JAN2002																														
<table border="1"> <tr> <td>DIMENSIONS: mm [INCHES]</td> <td>TOLERANCES UNLESS OTHERWISE SPECIFIED:</td> <td>PRODUCT SPEC</td> <td>NAME</td> </tr> <tr> <td>ϕ</td> <td>0 PLC ± -</td> <td>108-2085</td> <td>STANDARD RANGE WIRE TO 2.79 X 0.51 BARB SIAMEZE TERMINAL</td> </tr> <tr> <td></td> <td>1 PLC ± -</td> <td>APPLICATION SPEC</td> <td></td> </tr> <tr> <td></td> <td>2 PLC ± 0.13[.005]</td> <td></td> <td></td> </tr> <tr> <td></td> <td>3 PLC ± -</td> <td></td> <td></td> </tr> <tr> <td></td> <td>4 PLC ± -</td> <td></td> <td></td> </tr> <tr> <td></td> <td>ANGLES ± 2°</td> <td></td> <td></td> </tr> </table>			DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	NAME	ϕ	0 PLC ± -	108-2085	STANDARD RANGE WIRE TO 2.79 X 0.51 BARB SIAMEZE TERMINAL		1 PLC ± -	APPLICATION SPEC			2 PLC ± 0.13[.005]				3 PLC ± -				4 PLC ± -				ANGLES ± 2°		
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	NAME																											
ϕ	0 PLC ± -	108-2085	STANDARD RANGE WIRE TO 2.79 X 0.51 BARB SIAMEZE TERMINAL																											
	1 PLC ± -	APPLICATION SPEC																												
	2 PLC ± 0.13[.005]																													
	3 PLC ± -																													
	4 PLC ± -																													
	ANGLES ± 2°																													
MATERIAL BRASS, SPRING HARD	FINISH SEE TABLE	WEIGHT 0.000000	SIZE A2 CAGE CODE 00779 DRAWING NO C=1601005 RESTRICTED TO -																											
CUSTOMER DRAWING			SCALE 1:1 SHEET 1 OF 1 REV D6																											