





REVISIONS				
P	LTR	DESCRIPTION	DATE	APPV
A		REVISED PER ECO-17-014228	27SEP2017	SY SY



- 1 HOUSING MATERIAL: GLASS-FILLED POLYMER.
- 2 CONTACT MATERIAL: COPPER ALLOY.
- 3 CONTACT FINISH: DIN 41612 CLASS 2 IN CONTACT AREA. TIN PLATE ON TAILS.
- 4 PART NUMBER, DATE CODE, THIS APPROXIMATE AREA.
- 5 RECOMMENDED HOLE SIZE FOR MANUAL APPLICATION OF CONNECTOR ONTO PC BOARD.
- 6 MARKING ON THIS SIDE.



PC BOARD LAYOUT

SECTION X-X

ALL POSITIONS		* * * *				128	5536154-5
POSITIONS LOADED		Y	X	C	B	A	PART NUMBER
		ROWS LOADED				NO. OF LOADED POSITIONS	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN J. POLIGNONE 18APROS		TE Connectivity		ASSY, RECE, ENHANCED, TYPE C, EUROCARD, 5ROW, SOLDER, 3.30/3.43 WITH BOARD-LOCKS	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC		SIZE: A1 00779C=5536154	
0 PLC ± -		1 PLC ± -		2 PLC ± -		3 PLC ± 0.13 [.005]	
4 PLC ± -		ANGLES ± -		WEIGHT: 0.000000		SCALE: 4:1 SHEET 1 OF 1 REV A	
MATERIAL: 1 2		FINISH: 3		CUSTOMER DRAWING			