

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY - ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED PER ECO 10-024785	12-21-10	CT	BW
	B	REVISED PER ECO-15-010663	26AUG2015	RS	CT

33.6 REF

JACKNUT SUB-ASSEMBLY

M5 x 0.8

8.5 ACROSS FLATS

RETAINING NUT

1 JACKNUT SLEEVE, PLUNGER, CAP, RETAINING PIN, AND RETAINING NUT: STAINLESS STEEL PER AISI 316 OR AISI 316L
JACKNUT SPRING: STAINLESS STEEL PER AISI 302

2 THE KEY OF THE A-F JACKNUT ALIGNS WITH THE CORNER POINTS OF THE POLARIZING HEX.

3. THE JACKNUT AND RETAINING NUT ARE SHIPPED UNASSEMBLED. WHEN INSTALLING THESE ON A SHELL ASSEMBLY, LOCTITE® 272 THREADLOCKING ADHESIVE OR EQUIVALENT SHALL BE APPLIED. LOCTITE® IS A REGISTERED TRADEMARK OF HENKEL CORPORATION.


4. A SPANNER WRENCH TOOL, TYCO ELECTRONICS PART NUMBER 1738220-1 (WITH 1/4-IN ADAPTER) OR 1738221-1 (WITH T-HANDLE), IS USED TO LOCK THE RETAINING NUT. RECOMMENDED LOCKING TORQUE: 1.5 N-m [13 in-lb].

5. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS UNDER A LICENSE FROM RADIALL SA.

6 TE IDENTIFICATION LOCATED APPROXIMATELY AS SHOWN.

1738203-1

PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BW	11MAR2005	 TE Connectivity	
DIMENSIONS: mm		CHK JPM	11MAR2005		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD JPM	11MAR2005	NAME JACKNUT KIT, A-F GPRB2	
0 PLC ±-		PRODUCT SPEC	-	-	
1 PLC ±0.1		APPLICATION SPEC	-	-	
2 PLC ±-		WEIGHT	-	SIZE	A3
3 PLC ±-		CUSTOMER DRAWING		CAGE CODE	00779
4 PLC ±-		SCALE		DRAWING NO	G-1738203
ANGLES ±-		SHEET		RESTRICTED TO	-
FINISH		4:1		OF	1
MATERIAL		REV		B	

1470-19 (3/13)