

A

B

C

D

E

A

B

C

D

E

F

GUARNIZIONE, GOMMA SILICONICA
(GASKET, SILICONE RUBBER)



**DRAWING IS REPLACED BY
CUSTOMER DRAWING
282087**

1) PER RAPPRESENTAZIONE DIMA CONTROPARTE
VEDERE FOGLIO 2 DI 2.
(FOR COUNTERPART DETAIL SEE SHEET 2 OF 2)

LOGO "AMP"
("AMP" TRADE MARK)

AGGANCIO SECONDARIO, COLORE BIANCO, PRE-ASSEMBLATO
(SECONDARY LOCK, COLOUR WHITE, IN PRE-ASSEMBLED POSITION)

		PA 6.6 - GF20%			
BIANCO (WHITE)		ACC.TO IEC 60335-1		1745083-1	
FINITURA / COLORE (FINISH / COLOUR)		MATERIALE (MATERIAL)		NUMERO (PART NUMBER)	
CUSTOMER DWG. FOR REFERENCE ONLY			DISEGNO PER CLIENTE SOLO PER RIFERIMENTO		
THIS DRAWING IS UNPUBLISHED			RELEASE FOR PUBLICATION		19
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING					
TOLLERANZE: SE NON DIVERSAMENTE SPECIFICATO		DIAM. ISOLANTE (INS. DIA. RANGE)		RANGO FILO (WIRE RANGE)	
(TOLERANCES: UNLESS OTHERWISE SPECIFIED)		—		—	
± 0.3		 TE Connectivity			
ANGOLI (ANGLES)					
± 2°					
DIS. 10-4-2006 (DR.) M. PALMA		DESCRIZIONE 3 POS.PLUG ASS'Y (DESCRIPTION)			
CONT. 10-4-2006 (CHK) R. MARTINI		AMP SUPERSEAL 1.5 SERIES CONN.			
APP. 10-4-2006 (APP.) A. GENTA		LOC.	SIZE	NUMERO (DWG NO)	REV.
		I	A3	C-1745083	A3
					FOGLIO (SHEET)
					1 DI 2 (OF)



RAPPRESENTAZIONE DIMA CONTROPARTE
(COUNTERPART DETAIL AS SHOWN)

[illegible]