CATALOG # 1EBS1 SAFETY ORGANIZATIONS RELIABILITY SPECIFICATIONS: APPRVD DATE 0-15-02 STORAGE TEMPERATURE: -40°C TO +85°C THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED HUMIDITY: 21 DAYS @ 40°C 95% RH. BY THE LISTED AGENCY, THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED ECO-09-026495 AEG 05DEC 09 CURRENT OVERLOAD TEST: 6 TIMES I_r FOR 8 SECONDS IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET: TEST SPECIFICATIONS: UL RECOGNIZED: UL 1283 CSA CERTIFIED: CSA 22.2, # 8 INDUCTANCE: 10.0 mH NOMINAL CAPACITANCE: (MEASURED @ 1KHz, 0.250VAC MAX., 25°C±1°C) VDE APPROVED: VDE 565-3 LINE TO GROUND: 0.0058 µF ±20% OPERATING SPECIFICATIONS 0.0485 μF ±20% LINE TO LINE: DISCHARGE RESISTOR: 1.5M ∩ LINE CURRENT/VOLTAGE: 1 AMP, 120/250 VAC, L/G AND L/L I.R 1 AMP/40°C, 250 VAC NO DISCHARGE RESISTOR: 6000M₁ (MIN.) @ 100VDC, 20°C AND 50% RH LINE FREQUENCY: 50-60Hz MAXIMUM LEAKAGE CURRENT, RECOMMENDED RECEIVING INSPECTION HIPOT: EACH LINE TO GROUND: 0.22 mA@ 120V 60Hz LINE TO GROUND: 1500 VAC OR 2250 VDC FOR 1 MINUTE 0.38 mA@ 250V 50Hz LINE TO LINE: 1450 VDC FOR 1 MINUTE OPERATING AMBIENT TEMP, RANGE: -10°C TO +40°C @ RATED CURRENT, In. FILTER APPROVAL: IN AN AMBIENT, $\mathrm{T_{O}}$, HIGHER THAN 40°C, THE MAXIMUM OPERATING THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR CURRENT, In, IS AS FOLLOWS: 100 -Ta YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT. $I_0 = I_r -$ 0.250 FASTONS WITH-0.29 0.45Ø 0.069 HDLE — 1.35 MAX. —⇒ REF RFF (2X) 0 0.900 0.81 I I MAX. MAX. 1.185 2.20 ±.010 0.250 FASTON WITH 0.069 X 0.155 SLOT 1.10 PUNCH PANEL FROM OUTSIDE $^{\prime\prime}$ $\mathbb{A}^{\,\prime\prime}$ +.002 ⚠ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI 0.815 ±.002 R 0.188 (4X)PANEL CUTOUT (FRONT MOUNT) PANEL THICKNESS | PANEL CUTOUT "A" 1.260 0.031-0.052 1-6609005-1 0.046-0.068 1.350 1 1609005-1 OB SOLETE 1 50<u>n</u>-50 (MINIMUM) INSERTION THIRD ANGLE LDSSPROJECTION FREQUENCY 844 E. ROCKLAND RD. LIBERTYVILLE IL 60048 01 .05 0.1 .15 0.5 5 3 30 10 UNLESS OTHERWISE SPECIFIED. MHz TOLERANCE TO BE ±.025 POWER LINE FILTER COMMON MATERIAL & FINISH: AS SUPPLIED 12 23 29 32 41 47 47 47 40 This document is proprietary to CORCOM INC. CAD FILE: G:\CD\IEBS102 TYCO # 1-1609005-1 dΒ DATE: 8-10-02 REV. and is not to be reproduced nor used for ZTM DIFF. 3 3 14 23 41 47 50 44 nanufacturing purposes except on CORCOM'S 1EBS1 ORW. BY: ORIG: dΒ prior written consent.