



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ECO-20-012219	04SEP2020	GK	DR



1. STAMP AMP 22-18* APPROX AS SHOWN
WIRE RANGE IS 22 - 16 AWG
2. WIRE INSULATION DIAMETER: $\phi 2.667 - 3.556$ [$\phi .105-.140$]
3. BODY MATERIAL THK: 0.787 ± 0.051 [$.031 \pm .002$]
4. MATERIAL: BODY - CU PER ASTM B152
INSULATION - PVC
5. FINISH: BODY - TIN PLATE 0.00254 [$.000100$] MIN EXT THK PER ASTM B545
INSULATION COLOR - RED
6. APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE

100	RT015-040-V	1SET121004R0000	34148
QTY	DESIGNATION	ENTRELEC PN	TE PN

		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 04SEP2020 GOPALAKRISHNA HV CHK 04SEP2020 ROHDE DANIEL F APVD 04SEP2020 ROHDE DANIEL F PRODUCT SPEC UL 486A-B APPLICATION SPEC 114-2161 WEIGHT		ENTRELEC Electrical Solutions							
MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]		DIMENSIONS: mm [INCHES]		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± - 04SEP2020 ROHDE DANIEL F		NAME TERMINAL, RING TONGUE, PLASTI-GRIP WIRE SIZE, 22-16 AWG							
VOLTAGE RATING: 600V MAX (1000V FIXTURE OR SIGN)													
CIRCULAR MIL AREA: 0.26-1.65mm² [509-3260] SOLID OR STRANDED		MATERIAL - 		FINISH - 		SIZE A3		CAGE CODE 00779		DRAWING NO C-1SET121004R0000		RESTRICTED TO -	
CUSTOMER DRAWING						SCALE 4:1		SHEET 1 OF 1		REV A			