



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ECO-20-012219	07SEP2020	GK	DR



- 1 STAMP AMP 22-18* APPROX AS SHOWN
WIRE RANGE IS 22-16 AWG
2. WIRE INSULATION DIAMETER: $\varnothing 2.667 - 3.556$ [$\varnothing .105 - .140$]
3. BODY MATERIAL THK: 0.787 ± 0.051 [$.031 \pm .002$]
- 4 MATERIAL: BODY - CU PER ASTM B152
INSULATION - PVC
- 5 FINISH: BODY - TIN PLATE 0.00254 [$.000100$] MIN EXT THK PER ASTM B545
INSULATION COLOR - RED
- 6 APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE

100	RT015-060-V	1SET121006R0000	34150
QTY	DESIGNATION	ENTRELEC PN	TE PN

		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 07SEP2020 GOPALAKRISHNA HV		ENTRELEC Electrical Solutions							
MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]		DIMENSIONS: mm [INCHES] 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± -		CHK 07SEP2020 ROHDE DANIEL F		NAME TERMINAL, RING TONGUE, PLASTI-GRIP, WIRE SIZE, 22-16 AWG —					
						APVD 07SEP2020 ROHDE DANIEL F							
VOLTAGE RATING: 600V MAX (1000V FIXTURE OR SIGN)						PRODUCT SPEC UL 486A-B		SIZE A3					
						APPLICATION SPEC 114-2161							
CIRCULAR MIL AREA: 0.26-1.65mm² [509-3260] SOLID OR STRANDED		MATERIAL - 		FINISH - 		WEIGHT		GAGE CODE 00779		DRAWING NO C-1SET121006R0000		RESTRICTED TO —	
						CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1		REV A	