






REVISIONS				
P.	LTN.	DESCRIPTION	DATE	APVD.
-	-	SEE SHEET 1	-	-



RECOMMENDED MOUNTING HOLE PATTERN
 FOR 1.57±0.20 [0.062±.008] THICK P.C. BOARD

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 02JAN2002	TE Connectivity														
DIMENSIONS: mm [INCHES]		CHK D. BOSSI 02JAN2002															
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. BOSSI 02JAN2002	NAME MTA-100 HEADER ASSY, HIGH TEMP, FRICTION LOCK, .025 SQ STR POST, TIN OR TIN-LEAD PLATED, TUBE LOADED														
<table border="1"> <tr> <td>0 PLC</td> <td>±</td> </tr> <tr> <td>1 PLC</td> <td>±</td> </tr> <tr> <td>2 PLC</td> <td>±0.38 [0.015]</td> </tr> <tr> <td>3 PLC</td> <td>±</td> </tr> <tr> <td>4 PLC</td> <td>±</td> </tr> <tr> <td>ANGLES</td> <td>40° 30'</td> </tr> <tr> <td>FINISH</td> <td>-</td> </tr> </table>		0 PLC	±	1 PLC	±	2 PLC	±0.38 [0.015]	3 PLC	±	4 PLC	±	ANGLES	40° 30'	FINISH	-	APPLICATION SPEC	SIZE A100779
0 PLC	±																
1 PLC	±																
2 PLC	±0.38 [0.015]																
3 PLC	±																
4 PLC	±																
ANGLES	40° 30'																
FINISH	-																
MATERIAL		WEIGHT	SCALE 5:1 SHEET 2 OF 2 REV K4														
CUSTOMER DRAWING		SCALE 5:1	SHEET 2 OF 2														