



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ECO-20-012219	11SEP2020	GK	DR



- 1 STAMP AMP 16-14* LOCATE APPROX AS SHOWN
2. WIRE INSULATION DIAMETER: $\varnothing 2.997 - 4.902$ [$\varnothing .118-.193$]
3. BODY MATERIAL THK: 0.787 ± 0.051 [$.031 \pm .002$]
- 4 MATERIAL: BODY - CU PER ASTM B152
INSULATION - PVC
- 5 FINISH: BODY - TIN PLATE 0.00254 [$.000100$] MIN EXT THK PER ASTM B545
INSULATION COLOR - BLUE
- 6 APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE

100	SD025-050-V	1SET131007R0000	160171
QTY	DESIGNATION	ENTRELEC PN	TE PN

		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11SEP2020 GOPALAKRISHNA HV CHK 11SEP2020 ROHDE DANIEL F APVD 11SEP2020 ROHDE DANIEL F		ENTRELEC Electrical Solutions							
MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127 [.005] 4 PLC ± - ANGLES ± 1°		NAME TERMINAL, SPADE, PLASTI-GRIP, WIRE SIZE: 16 - 14 AWG —							
VOLTAGE RATING: 600V MAX (1000V FIXTURE OR SIGN)													
CIRCULAR MIL AREA: 1.04-2.52mm² [2050-5180] SOLID OR STRANDED		MATERIAL - 		FINISH - 		SIZE A3		CAGE CODE 00779		DRAWING NO C-1SET131007R0000		RESTRICTED TO —	
CUSTOMER DRAWING						SCALE 5:1		SHEET 1 OF 1		REV A			