


REVISIONS




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ECO-20-012219	21SEP2020	GK	DR

 Listed	 Certified
12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED



- 1. STAMP AMP 12-10\* APPROX AS SHOWN
- 2. WIRE INSULATION DIAMETER:  $\phi 3.810 - 6.350$  [ $\phi .150 - .250$ ]
- 3. BODY MATERIAL THK:  $0.991 \pm 0.051$  [ $.039 \pm .002$ ]
- 4. MATERIAL: BODY - CU PER ASTM B152  
INSULATION - PVC
- 5. FINISH: BODY - TIN PLATE  $0.00254$  [ $.000100$ ] MIN EXT THK PER ASTM B545  
INSULATION COLOR - YELLOW
- 6. APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE

100	SD060-060-V	1SET131010R0000	165019
QTY	DESIGNATION	ENTRELEC PN	TE PN

MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]  VOLTAGE RATING: 600V MAX (1000V FIXTURE OR SIGN)  CIRCULAR MIL AREA: 2.62-6.64mm <sup>2</sup> [5,180-13,100] SOLID OR STRANDED	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 21SEP2020 GOPALAKRISHNA HV	<b>ENTRELEC</b> Electrical Solutions  TERMINAL, SPADE, PLASTI-GRIP, WIRE SIZE:12-10 AWG
	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK 21SEP2020 ROHDE DANIEL F	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± -	APVD 21SEP2020 ROHDE DANIEL F	
	MATERIAL 	FINISH - 	PRODUCT SPEC UL 486A-B	
			APPLICATION SPEC 114-2161	NAME
			WEIGHT -	SIZE CAGE CODE DRAWING NO RESTRICTED TO
			CUSTOMER DRAWING	A3 00779 C-1SET131010R0000 -
				SCALE 6:1 SHEET 1 OF 1 REV A