


- 2 .065/.061 DIMENSION MAY GO TO .067 ON POSTS WITH AN A DIMENSION OF 1.187 OR LONGER.
- 3 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 4 .000100-.000200 BRIGHT TIN-LEAD OVER .000030 NICKEL.
- 5 .000030 GOLD IN AREA D, GOLD FLASH ON REMAINDER OF POST, ALL OVER .000050 NICKEL.
- 6 .000015 GOLD IN AREA D, GOLD FLASH ON REMAINDER OF POST, ALL OVER .000050 NICKEL.
- 7 .000050 GOLD OVER .000050 NICKEL OVER ENTIRE POST.
- 8 .000015 GOLD IN AREA D, .000100-.000200 BRIGHT TIN-LEAD ON SOLDER AREA, WITH ENTIRE POST UNDERPLATED .000050 NICKEL.
- 9 .000030 GOLD IN AREA D, .000100-.000200 BRIGHT TIN-LEAD ON SOLDER AREA, WITH ENTIRE POST UNDERPLATED .000050 NICKEL.
- 10 OBSOLETE PART NUMBER.
- 11 .000100-.000200 MATTE TIN OVER .000030 NICKEL.
- 12 PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
- 13 ROHS 2002/95/EC COMPLIANT.



FINISH	E	D	C	B	A	LOOSE PIECE PART NO	PART NUMBER
13	-	-	.200	.825	.587	-	7-85842-0
11	-	-	.200	1.430	1.187	-	6-85842-1
11	-	-	.200	.990	.750	-	5-85842-8
11	-	-	.200	1.550	1.310	-	5-85842-5
11	-	-	.200	.645	.405	5-85832-1	5-85842-2
11	-	-	.200	.837	.587	-	4-85842-6
11	-	-	.200	.655	.405	-	4-85842-5
4	-	.950	.500	1.300	1.062	2-86211-3	4-85842-4
9	.145	1.200	.700	1.550	1.310	2-86211-2	4-85842-3
9	.145	1.080	.500	1.430	1.187	2-86211-1	4-85842-2
9	.145	.950	.500	1.300	1.062	2-86211-0	4-85842-1
9	.145	.765	.400	1.115	.875	1-86211-9	4-85842-0
9	.145	.640	.300	.990	.750	1-86211-8	3-85842-9
9	.145	.550	.300	.900	.662	1-86211-7	3-85842-8
8	.145	.475	.200	.825	.587	1-86211-6	3-85842-7
9	.145	.475	.200	.825	.587	1-86211-5	3-85842-6
9	.145	.295	.100	.845	.405	85832-8	3-85842-5
9	.145	.295	.100	.645	.405	85832-7	3-85842-4
6	-	1.080	.500	1.430	1.187	1-86211-4	3-85842-3
6	-	.640	.300	.990	.750	1-86211-3	3-85842-2
6	-	1.200	.700	1.550	1.310	1-86211-2	3-85842-1
4	-	-	.200	1.115	.875	1-86211-1	3-85842-0
7	-	.950	.500	1.300	1.062	1-86211-0	2-85842-8
6	-	-	.200	.645	.405	85832-6	2-85842-7
6	-	.190	.100	.540	.300	86211-9	2-85842-6
4	-	-	.200	.540	.300	86211-8	2-85842-4
6	-	-	.200	1.550	1.310	85841-4	2-85842-3
6	-	.475	.200	.825	.587	86211-7	2-85842-2
5	-	1.080	.500	1.430	1.187	86211-6	2-85842-1
4	-	-	.200	.825	.587	86211-5	2-85842-0
6	-	-	.200	.990	.750	85876-3	1-85842-9
5	-	.475	.200	.825	.587	86211-4	1-85842-8
5	-	.765	.400	1.115	.875	86211-3	1-85842-6
6	-	.295	.100	.645	.405	85832-5	1-85842-4
5	-	.550	.300	.900	.662	86211-2	1-85842-3
4	-	-	.200	1.430	1.187	86211-1	1-85842-1
5	-	.640	.300	.990	.750	85876-2	85842-9
4	-	-	.200	.990	.750	85876-1	85842-8
5	-	1.200	.700	1.550	1.310	85841-2	85842-6
4	-	-	.200	1.550	1.310	85841-1	85842-5
5	-	.295	.100	.645	.405	85832-2	85842-3
4	-	-	.200	.645	.405	85832-1	85842-2

THIS DRAWING IS A CONTROLLED DOCUMENT.

APPROVED: KATE HELM 10JUL89  
 CHK: H. MOLL 17JUL89  
 NAME: SAM BEAM 17JUL89

**STE** TE Connectivity

CONTACT, MOD 1 MALE, (.031x.062)

APPLICATION SPEC: -  
 SIZE: A1  
 CAGE CODE: 00779  
 DRAWING NO: 85842  
 WEIGHT: -  
 MATERIAL: -  
 FINISH: -

CUSTOMER DRAWING SCALE: 20:1 SHEET: 1 OF 1 REV: U2