

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,1999 .

© COPYRIGHT 1999

BY AMP KOREA.

ALL RIGHTS RESERVED.

LOC  
DS

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
O		RELEASED (PER FC00-0099-98)	19/NOV/98	YM	CS
A		REVISED (PER FC00-0065-99)	24/MAY/99	YM	CS

D

SECTION "B-B"

C

SECTION "C-C"

B

SECTION "A-A"

A

\* NOTES;

- TAB CONTACT P/N 171631.
- CUSTOMER MANUAL. CM-325J
- WIRE SIZE EQUIV AVS 0.2~0.5 sqmm.
- ④ INSULATION DIA RANGE 1.4 ~2.4mm

THIS DRAWING IS CONTROLLED DOCUMENT FOR AMP KOREA.  
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING  
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: MM

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:
 $0 < XX < 10 \pm 0.2$   
 $10 \leq XX < 30 \pm 0.25$   
 ANGLES  $\pm 3^\circ$ 


MATERIAL  
COPPER ALLOY  
0.3THK.FINISH  
PRE-TINNED

DWN YM CHOI 24.MAY'99

CHK JK SONG 24.MAY'99

APVD CS LEE 24.MAY'99

PRODUCT SPEC

④ 108-61022

APPLICATION SPEC

④ 114-61000, 61012

WEIGHT  
NET; 0.35gf
 AMP KOREA.  
kyungsan, korea
NAME  
.070 TYPE EJ MK-II+ RECEPTACLE.

SIZE	CAGE CODE	DRAWING NO
A3	00779	④ 9 3 6 0 1 9

SCALE 10/1 SHEET 1 OF 1 REV A

AMP 1470-19 REV 09MAY94