



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ECO-20-012219	21SEP2020	GK	DR

 Listed	 Certified
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED



- 1 STAMP AMP 16-14* APPROX AS SHOWN
2. WIRE INSULATION DIAMETER: $\varnothing 2.997 - 4.902$ [$\varnothing .118 - .193$]
3. BODY MATERIAL THK: 0.787 ± 0.051 [$.031 \pm .002$]
- 4 MATERIAL: BODY - CU PER ASTM B152
INSULATION - PVC
- 5 FINISH: BODY - TIN PLATE 0.00254 [$.000100$] MIN EXT THK PER ASTM B545
INSULATION COLOR - BLUE
- 6 APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE

100	SDF025-035-V	1SET132004R0000	324165
QTY	DESIGNATION	ENTRELEC PN	TE PN

	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 21SEP2020 GOPALAKRISHNA HV CHK 21SEP2020 ROHDE DANIEL F APVD 21SEP2020 ROHDE DANIEL F PRODUCT SPEC UL 486A-B APPLICATION SPEC 114-2161 WEIGHT -		ENTRELEC Electrical Solutions				
MAX RECOMMENDED OPERATING TEMPERATURE: 105°C[221°F]	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME TERMINAL, SPADE, FLANGED, PLASTI-GRIP, WIRE SIZE:16-14 AWG					
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± -							
VOLTAGE RATING: 600V MAX (1000V FIXTURE OR SIGN)		FINISH		SIZE		CAGE CODE	DRAWING NO		RESTRICTED TO
CIRCULAR MIL AREA: 1.04-2.62mm² [2,050-5,180] SOLID OR STRANDED		- 		A3		00779	C-1SET132004R0000		-
CUSTOMER DRAWING					SCALE		SHEET		REV
					6:1		1 OF 1		A