



## ABS HOUSING FOR DISPLAY CONDITIONER

- Table case for Display electronic
- Electrical electronic dimension 96x48 mm
- Protection IP40
- Available as standard with Europe power cable (other cables on request)

### Features

- ABS housing
- Accepts display and conditioner/display devices
- Optional Voltage output
- Optional RS 232 interface

### Applications

- Laboratory design for conditioners
- Transportable measurement systems

### DESCRIPTION

Measurement Specialties, Inc. offers comprehensive measurement solutions including electronic signal conditioning and display units.

The ABS table case allows integrating a conditioning unit with dimensions of 96 x 48 mm. The standard version is supplied with a connexion set (power supply, connecting sensor and analogue output)


A second version of this case The ABS case is suitable to the Measurement Specialties, Inc. complete range of conditioners **Alpha, Beta, Gamma ; M905, M210 and MMP210.**

## CHARACTERISTICS

### Mechanical characteristics

Dimensions (H x L x W)	155 x 65 x 165 mm
<b>ABS housing</b>	
Colour	Beige
Aspect	Texture
<b>Front/Rear panels ABS housing</b>	
Colour	Black
Weight (without the electronic)	600 gr
<b>Equipment front panel</b>	
Power Switch A/M (for Arrêt / Marche)	On/Off LED
Calibration button	(optional)
<b>Equipment rear panel</b>	
Fuse (350 mA)	Connector access for easy replacement
Power Voltage cable	Europe plug as standard
Analogue output on BNC connector	(mating plug not supplied)
Sensor connector	Din7 wires female, mating connector supplied


## DIMENSIONS (IN METRIC)



### Notes:

1. SA connector is always present on ABS housings (it is not active if there is no analogue output with the electronic display).
2. Switches connector are not present if there is no thresholds option with the electronic display.
3. RS232 connector is not present if the option was not ordered with the electronic.

**CONNECTORS WIRING**



Important! All wirings pictures represent the soldering face of the mating plug.

Pin	Sensor	SA (Analogue Output)	RS232	Thresholds
1	+ Power Supply	+ Signal (internal)	Ground	Rest HT
2	- Measure	- Signal (external)	Rd	Common HT
3	- Power Supply		Td	Work HT
4	+ Measure		-	Rest LT
5	NC		-	Common LT
6	NC		-	Work LT
7	Shield		Common (0v)	

**NORTH AMERICA**

Measurement Specialties, Inc.,  
 a TE Connectivity Company  
 Phone: +1 800 522 6752  
 Email: [customercare.hmpt@te.com](mailto:customercare.hmpt@te.com)

**EUROPE**

Measurement Specialties (Europe), Ltd.  
 a TE Connectivity Company  
 Phone: +31 73 624 6999  
 Email: [customercare.lcsb@te.com](mailto:customercare.lcsb@te.com)

**ASIA**

Measurement Specialties (China), Ltd.,  
 a TE Connectivity Company  
 Phone +86 400 820 6015  
 Email: [customercare.shzn@te.com](mailto:customercare.shzn@te.com)

[te.com/sensorsolutions](http://te.com/sensorsolutions)

Measurement Specialties, MEAS, American Sensor Technologies, AST, TE Connectivity, TE, and the TE Connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Other logos, products and/or company names referred to herein may be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2018 TE Connectivity Ltd. family of companies All Rights Reserved.