

## 623 Bulkhead connector

12-pin insulation insert Code 0° housing code 1 flange mount /Flange 25x25

## **Technical Data**

number of pins temperature range

-20 °C to 130 °C

when connected IP 66/67 protection type

**Electrical Data** rated current

signal max. 7 A\* 160 V (AC/DC)

500

rated voltage rated insulation voltage (L-L) 2500 V

Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

pollution degree over voltage category max. height for operation III 2000 m

**Material** 

mating cycles

zinc diecast / nickel plated

PBT, UL 94 / V0 insulation insert

Contacts (not part of product contents)

Tools (not part of product contents)

A DF A 012 NN 00 00 0151 000 A D A 012 N 00 00 0151 000



**Contact Arrangement** mating view




© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH Bernrieder Straße 15 94559 Niederwinkling, Deutschland Tel.: +49 9962 2002-0 Fax: +49 9962 2002-70 E-Mail: intercontec@te.com Web: www.intercontec.biz





**Main Dimensions** Bulkhead connector

\*for max. wire cross-section pay attention to the cross-section of used contacts