

623 Receptacle angled rotatable

speedtec

17-pin insulation insert Code 0° housing code 1 flange mount /Flange 28x28

Technical Data

number of pins 17
temperature range -20 °C to 130 °C
protection type when connected IP 66/67
rotation range 330°

Electrical Data signal rated current max. 7 A* rated voltage 125 V (AC/DC) rated insulation voltage (L-L) 2000 V

mating cycles 500

Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

pollution degree 3 over voltage category III max. height for operation 2000 m

Material housing zinc diecast / chromated

insulation insert PBT, UL 94 / V0

seals FKM

Contacts (not part of product contents)

Tools (not part of product contents)

A ED C 139 NN 00 00 1100 000 A G C 139 N 00 00 1100 000



Contact Arrangement mating view



© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH Bernrieder Straße 15 94559 Niederwinkling, Deutschland Tel.: +49 9962 2002-0 Fax: +49 9962 2002-70 E-Mail: intercontec@te.com Web: www.intercontec.biz



