


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ECO-20-012219	13NOV2020	GK	DR

 Listed	 Certified
12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED



- 1 STAMP 8S AMP 12-10\* APPROX AS SHOWN
- 2. WIRE INSULATION DIAMETER:  $\phi 2.667 - 5.080$  [ $\phi .105 - .200$ ]
- 3. BODY MATERIAL THK:  $1.016 \pm 0.051$  [ $.040 \pm .002$ ]
- 4 MATERIAL: BODY - BRASS PER ASTM B36  
INSULATION - PVC
- 5 FINISH: BODY - TIN PLATE  $0.00254$  [ $.000100$ ] MIN EXT THK PER ASTM B545  
INSULATION COLOR - YELLOW
- 6 APPLIES FROM EDGE OF METAL WIRE BARREL TO CENTER OF STUD HOLE

100	SDL060-040-V	1SET134007R0000	52474
QTY	DESIGNATION	ENTRELEC PN	TE PN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GOPALAKRISHNA HV 18NOV2020	<b>ENTRELEC</b> Electrical Solutions	
DIMENSIONS: mm [INCHES]		CHK ROHDE DANIEL F 18NOV2020		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD ROHDE DANIEL F 18NOV2020	NAME TERMINAL, SPRING SPADE, LONG, PLASTI-GRIP, WIRE SIZE :12-10 AWG	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± -		PRODUCT SPEC UL 486A-B	DRAWING NO 114-2161	
MATERIAL - 4		FINISH - 5	SIZE A3	CAGE CODE 00779
MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]		RESTRICTED TO -		SCALE 6:1
VOLTAGE RATING: 600V MAX (1000V FIXTURE OR SIGN)		DRAWING NO C-1SET134007R0000		SHEET 1 OF 1
CIRCULAR MIL AREA: 2.62-6.64mm² [5,180-13,100] SOLID OR STRANDED		CUSTOMER DRAWING		REV A