

623 Extension

speedtec

17-pin insulation insert uncoded housing code 1 **EMC - Shielding**

A KU A 034 NN 00 40 0100 000 A K A 034 N 00 40 0100 000



Contact Arrangement mating view



Contacts (not part of product contents)

Tools (not part of product contents)


© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH Bernrieder Straße 15 94559 Niederwinkling, Deutschland Tel.: +49 9962 2002-0 Fax: +49 9962 2002-70 E-Mali: intercontec@te.com Web: www.intercontec.biz





Main Dimensions Extension

*for max. wire cross-section pay attention to the cross-section of used contacts

protection type **Electrical Data** rated current rated voltage

Technical Data number of pins temperature range

clamping range

signal max. 7 A* 125 V (AC/DC) 2000 V rated insulation voltage (L-L)

mating cycles

pollution degree

Material

housing insulation insert seals clamp ring

over voltage category max. height for operation

500

2000 m

3 III

FKM

Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

17

-20 °C to 130 °C

Ø 9.0 mm to Ø 13.2 mm when connected IP 66/67

zinc diecast / nickel plated PBT, UL 94 / V0

brass / nickel plated