



ANT-915-NUB-ccc

915 MHz LPWA Whip Antenna

The ANT-915-NUB-ccc is an extremely compact whip-style antenna designed for sub-1 GHz and low-power, wide-area (LPWA) applications including LoRaWAN®, IoT, remote controls, and ISM band applications in the 902 MHz to 930 MHz range.

The ANT-915-NUB-ccc is a rugged monopole antenna with a length of less than 18 mm. The ANT-915-NUB-ccc may be used with metallic and non-metallic enclosures. The antenna connects using an SMA plug (male pin) or RP-SMA plug (female socket) connector.

FEATURES

- Performance at 902 MHz to 930 MHz
 - VSWR: ≤ 2.6
 - Peak Gain: 3.9 dBi
 - Efficiency: 38%
- Compact size
 - Height 17.7 mm (0.70 in)
 - Diameter 7.0 mm (0.28 in)
- AEC-Q200 Grade 2 compliance
- Omnidirectional radiation pattern
- SMA plug (male pin) or RP-SMA plug (female socket) connection

APPLICATIONS

- Low-power, wide-area (LPWA) applications
 - LoRaWAN®, ITU-T Y.4480
- ISM applications
- Drone Antenna
- FPV Antenna
- UAV Antenna
- Remote control, sensing and monitoring
 - Security systems
 - Industrial machinery
 - Automated equipment
 - AMR (automated meter reading)
- Internet of Things (IoT) devices
- Smart Home networking
- Hand-held devices

ORDERING INFORMATION

Part Number	Description
ANT-915-NUB-RPS	915 MHz LPWA whip antenna with RP-SMA plug (female socket) connector
ANT-915-NUB-SMA	915 MHz LPWA whip antenna with SMA plug (male pin) connector

Available from Linx Technologies and select distributors and representatives.

TABLE 1. ELECTRICAL SPECIFICATIONS

ANT-915-NUB	915 MHz		
Frequency Range	902 MHz to 930 MHz		
VSWR (max)	2.6		
Peak Gain (dBi)	3.9		
Average Gain (dBi)	-4.3		
Efficiency (%)	38		
Polarization	Linear	Radiation	Omnidirectional
Max Power	25 W	Wavelength	1/4-wave
Electrical Type	Monopole	Impedance	50 Ω

Electrical specifications and plots measured at the edge of a 102 mm x 102 mm (4 in x 4 in) reference ground plane.

TABLE 2. MECHANICAL SPECIFICATIONS

Parameter	Value
Connection	SMA plug (male pin), RP-SMA plug (female socket)
Dimensions	17.7 mm x \varnothing 7.0 mm (0.70 in x \varnothing 0.28 in)
Weight	2.9 g (0.10 oz)
Operating Temp. Range	-40 °C to +105 °C

PRODUCT DIMENSIONS




Figure 1. ANT-915-NUB-ccc Antenna Dimensions

PACKAGING INFORMATION

The ANT-915-NUB antenna is individually packaged in a sealed plastic bag, 50 pcs packed in a labeled clear polyethylene bag. Distribution channels may offer alternative packaging options.

COUNTERPOISE

Quarter-wave or monopole antennas require an associated ground plane counterpoise for proper operation. The size and location of the ground plane relative to the antenna will affect the overall performance of the antenna in the final design. When used in conjunction with a ground plane smaller than that used to tune the antenna, the center frequency typically will shift higher in frequency and the bandwidth will decrease. The proximity of other circuit elements and packaging near the antenna will also affect the final performance.

For further discussion and guidance on the importance of the ground plane counterpoise, please refer to Linx Application Note, *AN-00501: Understanding Antenna Specifications and Operation*.

ANTENNA ORIENTATION

The ANT-915-NUB-ccc antenna is characterized in two antenna orientations as shown in Figure 2. The antenna in a free space orientation characterizes use of an antenna attached to an enclosure-mounted connector which is connected by cable to a printed circuit board. Characterization at the edge of the ground plane (102 mm x 102 mm) provides insight into antenna performance when attached to a connector on a metal enclosure. The two orientations represent the most common end-product use cases.




Figure 2. ANT-915-NUB-ccc Test Orientation

EDGE OF GROUND PLANE

The charts on the following pages represent data taken with the antenna oriented at the edge of the ground plane, as shown in Figure 3.



Figure 3. ANT-915-NUB-ccc on Edge of Ground Plane

VSWR

Figure 4 provides the voltage standing wave ratio (VSWR) across the antenna bandwidth. VSWR describes the power reflected from the antenna back to the radio. A lower VSWR value indicates better antenna performance at a given frequency. Reflected power is also shown on the right-side vertical axis as a gauge of the percentage of transmitter power reflected back from the antenna.




Figure 4. VSWR for ANT-915-NUB-ccc, Edge of ground Plane

RETURN LOSS

Return loss (Figure 5), represents the loss in power at the antenna due to reflected signals. Like VSWR, a lower return loss value indicates better antenna performance at a given frequency.




Figure 5. Return Loss for ANT-915-NUB-ccc, Edge of ground Plane

PEAK GAIN

The peak gain across the antenna bandwidth is shown in Figure 6. Peak gain represents the maximum antenna input power concentration across 3-dimensional space, and therefore peak performance, at a given frequency, but does not consider any directionality in the gain pattern.




Figure 6. Peak Gain for ANT-915-NUB-ccc, Edge of ground Plane

AVERAGE GAIN

verage gain (Figure 7), is the average of all antenna gain in 3-dimensional space at each frequency, providing an indication of overall performance without expressing antenna directionality.




Figure 7. Antenna Average Gain for ANT-915-NUB-ccc, Edge of ground Plane

RADIATION EFFICIENCY

Radiation efficiency (Figure 8), shows the ratio of power delivered to the antenna relative to the power radiated at the antenna, expressed as a percentage, where a higher percentage indicates better performance at a given frequency.





Figure 8. Antenna Radiation Efficiency for ANT-915-NUB-ccc, Edge of ground Plane

RADIATION PATTERNS

Radiation patterns provide information about the directionality and 3-dimensional gain performance of the antenna by plotting gain at specific frequencies in three orthogonal planes. Antenna radiation patterns (Figure 9), are shown using polar plots covering 360 degrees. The antenna graphic above the plots provides reference to the plane of the column of plots below it. Note: when viewed with typical PDF viewing software, zooming into radiation patterns is possible to reveal fine detail.

RADIATION PATTERNS - EDGE OF GROUND PLANE



902 MHz TO 930 MHz (915 MHz)




Figure 9. Radiation Patterns for ANT-915-NUB-ccc Antenna, Edge of ground Plane

FREE SPACE - NO GROUND PLANE

The charts on the following pages represent data taken with the antenna in free space, no ground plane, as shown in Figure 10.



Figure 10. ANT-8/9-IPW2-NP at Center of Ground Plane

VSWR

Figure 11 provides the voltage standing wave ratio (VSWR) across the antenna bandwidth. VSWR describes the power reflected from the antenna back to the radio. A lower VSWR value indicates better antenna performance at a given frequency. Reflected power is also shown on the right-side vertical axis as a gauge of the percentage of transmitter power reflected back from the antenna.




Figure 11. VSWR for ANT-915-NUB-ccc Antenna in Free Space

RETURN LOSS

Return loss (Figure 12), represents the loss in power at the antenna due to reflected signals. Like VSWR, a lower return loss value indicates better antenna performance at a given frequency.




Figure 12. Return Loss for ANT-915-NUB-ccc Antenna in Free Space

PEAK GAIN

The peak gain across the antenna bandwidth is shown in Figure 13. Peak gain represents the maximum antenna input power concentration across 3-dimensional space, and therefore peak performance, at a given frequency, but does not consider any directionality in the gain pattern.




Figure 13. Peak Gain for ANT-915-NUB-ccc Antenna in Free Space

AVERAGE GAIN

Average gain (Figure 14), is the average of all antenna gain in 3-dimensional space at each frequency, providing an indication of overall performance without expressing antenna directionality.




Figure 14. Antenna Average Gain for ANT-915-NUB-ccc Antenna in Free Space

RADIATION EFFICIENCY

Radiation efficiency (Figure 15), shows the ratio of power delivered to the antenna relative to the power radiated at the antenna, expressed as a percentage, where a higher percentage indicates better performance at a given frequency.




Figure 15. Antenna Radiation Efficiency for ANT-915-NUB-ccc Antenna in Free Space

RADIATION PATTERNS

Radiation patterns provide information about the directionality and 3-dimensional gain performance of the antenna by plotting gain at specific frequencies in three orthogonal planes. Antenna radiation patterns (Figure 16), are shown using polar plots covering 360 degrees. The antenna graphic above the plots provides reference to the plane of the column of plots below it. Note: when viewed with typical PDF viewing software, zooming into radiation patterns is possible to reveal fine detail.

RADIATION PATTERNS - FREE SPACE (NO GROUND PLANE)




Figure 16. Radiation Patterns for ANT-915-NUB-ccc Antenna in Free Space

TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

te.com

TE Connectivity, TE, TE connectivity (logo), Linx and Linx Technologies are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

TE Connectivity warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations TE Connectivity will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the TE Connectivity product is installed. Useful lifetime of the original end product may vary but is not warranted to exceed one (1) year from the original date of the end product purchase.

©2022 TE Connectivity. All Rights Reserved.

10/22 Original