

THIS DRAWING IS A CONTROLLED DOCUMENT.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	PRODUCTION ISSUE	04JUL2017	KH	AP





THIS IS A TRIMMED VARIANT
MODIFIED DIMENSIONS ARE SHOWN THUS:– #

Part No.	H Min a	H Max b	J Min a	J Max b	P ±5% a	P ±10% b	R ±10% b	S Ref b	T Ref b	U Min a	U ±20% b	JO Ref b	HW ±30% b	JW ±30% b
202S132–100C–01–0	20 [.79]	14.2 [.56]	12 [.47]	6.0 [.24]	47 [1.85]	47 [1.85]	15 [.59]	3.0 [.12]	1.0 [.04]	6.0 [.24]	10 [.39]	17 [.67]	2.0 [.08]	1.0 [.04]
202S142–100C–01–0	26 [1.02]	18.0 [.71]	14 [.55]	7.2 [.28]	55 [2.17]	55 [2.17]	15 [.59]	3.0 [.12]	1.0 [.04]	6.0 [.24]	10 [.39]	20 [.79]	2.0 [.08]	1.0 [.04]
202S152–100C–01–0	32 [1.26]	22.4 [.88]	20 [.79]	8.5 [.33]	69 [2.72]	69 [2.72]	15 [.59]	3.0 [.12]	1.0 [.04]	9.0 [.35]	15 [.59]	25 [.98]	2.0 [.08]	1.0 [.04]
202S174–100C–01–0	41 [1.61]	35.1 [1.38]	32 [1.26]	15.8 [.62]	108 [4.25]	110 [4.33]	45 [1.77]	3.0 [.12]	1.7 [.07]	12.0 [.47]	20 [.79]	30 [1.18]	3.0 [.12]	1.5 [.06]
					#	#	#							

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,-,-.
© COPYRIGHT 2017 By TE Connectivity ALL RIGHTS RESERVED.

DIMENSIONS: mm[INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± –
4 PLC ± –
ANGLES ± –

DWN K. HOLAL 04JUL2017
CHK N. NAGAR 04JUL2017
APVD A. POOLE 04JUL2017

PRODUCT SPEC —

APPLICATION SPEC —

WEIGHT

MATERIAL –

FINISH –

TE Connectivity

NAME
STRAIGHT BOOT, COATED
202S1XX–100C–01–0

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A4	00779	202S1XX–100C–01–0	—

CUSTOMER DRAWING

SCALE DNS SHEET 1 OF 2 REV 1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	–	SEE SHEET 1	–	—	—

COMPATIBILITY CHART

Material Dash No.	Material Description	SPEC No.	Coating Slash No.
–100C	POLYOLEFIN/SILVER COMPOSITE (ZEROHAL™)	RW–3046	/86, /200

ORDERING INFORMATION

202S1**–100C–01/**–0

- Adhesive Slash Number
- Modification Number
- Material Dash Number (see compatibility chart)
- Base Part Number

NOTES

1. As supplied dimensions are for parts without adhesive, when an adhesive layer is added entry diameters will reduce by 1.5mm Max.

2. For method of measuring recovered diameter, see appropriate RW specification (SPEC No.) section 2.2.

3. ZEROHAL is a trademark of TE Connectivity.

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION –,–. © COPYRIGHT 2017 By TE Connectivity ALL RIGHTS RESERVED.

DIMENSIONS: mm[INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± –
4 PLC ± –
ANGLES ± –

DWN K. HOLAL	04JUL2017	MATERIAL –	FINISH –
CHK N. NAGAR	04JUL2017	TE Connectivity	
APVD A. POOLE	04JUL2017		
PRODUCT SPEC —		NAME STRAIGHT BOOT, COATED 202S1XX–100C–01–0	
APPLICATION SPEC —		SIZE A4 / CAGE CODE 00779 / DRAWING NO C– 202S1XX–100C–01–0	RESTRICTED TO —
WEIGHT		CUSTOMER DRAWING	SCALE DNS / SHEET 2 OF 2 / REV 1