





WARNING - THIS DOCUMENT CONTAINS TECHNOLOGY WHOSE EXPORT IS RESTRICTED BY THE EXPORT ADMINISTRATION REGULATIONS ("EAR") PURSUANT TO 15 C.F.R. PARTS 730-774. VIOLATIONS OF THE EAR ARE SUBJECT TO SEVERE CRIMINAL PENALTIES UNDER THE EXPORT CONTROL REFORM ACT, AS AMENDED (TITLE 50, U.S.C., SEC. 4801, ET SEQ.).

REVISIONS				
P	LTR	DESCRIPTION	DATE	APPROV
L		REVISED PER ECN-24-272102	24JUN2024	PE DS



- .040 DIA HOLE IS RECOMMENDED FOR P.C. BOARD.
- CONNECTOR MATES WITH ANY AMP 62 POSN PLUG.
- REPLACEMENT SOCKET AMP# 207684-4.
- FINISH: CADMIUM PER QQ-P-614.
- FINISH: ZINC PER ASTM-B-633 .000200-.000400 THK WITH SUPPLEMENTARY CHROMATE (Cr3+).

REMARKS	DIM A	PART NO.
5	.025	5-208875-1
4	.025	208875-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 1-8-88	C.C. THOMAS	
DIMENSIONS: INCHES		1-25-88	F.C. BALLEW III	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		1-25-88	F. BALLEW	
0. PLC	± .005	NAME		
1. PLC	± .005	AMP#		
2. PLC	± .005	PRODUCT SPEC		
3. PLC	± .005	APPLICATION SPEC		
4. PLC	± .005	SIZE		
ANGLES	± .005	CAGE CODE		
MATERIAL	SEE CALLOUTS	DRAWING NO		
WEIGHT	---	A1 00779 C=208875		
CUSTOMER DRAWING		RESTRICTED TO		
SCALE 4:1		SHEET 1 of 1		