

DRAWING NO: FAD1705-1780-7-C


THIS DRAWING IS A CONTROLLED DOCUMENT



CATALOGUE NUMBER: FAD1705-1780-7 SUITS CONDUCTOR

DEADEND

STRANDING	COND. TYPE	DIAMETER	FITTING LAY
19/3.50	AAC/AAAC	17.50	RIGHT HAND
37/2.50	AAC/AAAC	17.50	RIGHT HAND
19/3.75 COMPACTED	AAC/AAAC	17.50	RIGHT HAND
COVERED CONDUCTOR XLPE	AAC/AAAC	17.05-17.80	RIGHT HAND



TECHNICAL SPECIFICATIONS:

CATALOGUE NUMBER: FAD1705-1780-7
DESCRIPTION: FULL-TENSION ALUMINIUM DEADEND
MATERIAL: ALUMINIUM ALLOY
NUMBER OF RODS: 5
ROD DIAMETER: 4.87mm
OVERAL LENGTH: 1215mm
END FINISH: BALLENDDED
FITTING LAY DIRECTION: RIGHT HAND
COLOUR CODED: BLUE

PRODUCT LABEL

FAD1705-1780-7
 19/3.50 & 37/2.50 AAC/AAAC
 19/3.75 COMPACTED AAC/AAAC
 XLPE 17.05-17.80

WEIGHT: 0.65kg
BATCH NO:
MONTH/YEAR:

BOX LABEL

P/N: FAD1705-1780-7
ID:
DESCRIPTION:
FULL-TENSION ALUMINIUM DEADEND
 19/3.50 & 37/2.50 AAC/AAAC
 19/3.75 COMPACTED AAC/AAAC
 XLPE 17.05-17.80
RANGE: 17.05 - 17.80
COLOUR-CODE: BLUE
QTY: 10 **WEIGHT:** **BATCH:**

LOC	REV	DESCRIPTION	DATE	DWN	APVD	MATERIAL NO	MATL SPEC/STD/DRG NO	PROCESS SPEC HEAT TREAT/PLATING NO	SIZE	PROJECTION	SCALE	DRAWING NO	SHEET	OF	REV
	2	CONDUCTOR 19/3.50 ADDED TO TABLE	04-06-2016	RN	AT				A3	3RD ANGLE	NTS	FAD1705-1780-7-C	1	1	2
DIST	1	NEW RELEASE	10-05-2013	RN	AT										
		REVISION RECORD													

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TE CONNECTIVITY PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TE CONNECTIVITY CORPORATION, AUSTRALIA.