




CATALOGUE NUMBER: FGD1600-1640-8 SUITS CONDUCTOR

DEADEND

STRANDING	COND. TYPE	DIAMETER	FITTING LAY
19/3.25	SC/GZ	16.25	RIGHT HAND
19/10	SC/GZ	16.26	RIGHT HAND




TECHNICAL SPECIFICATIONS:

CATALOGUE NUMBER: FGD1600-1640-8
DESCRIPTION: FULL-TENSION GALVANISED STEEL DEADEND
MATERIAL: HEAVILY GALVANISED STEEL WIRE
NUMBER OF RODS: 6
ROD DIAMETER: 4.47mm
OVERAL LENGTH: 1285mm
END FINISH: CHAMFERED
FITTING LAY DIRECTION: RIGHT HAND
COLOUR CODED: ORANGE

PRODUCT LABEL



BOX LABEL



LOC							IMPLIED NOTES BURRS AND SHARP EDGES REMOVED SCREW THREADS ARE TO AS 1275 DO NOT WORK TO DIMS MARKED REF SURFACE FINISH 6.3 U.N.O. DIMS ARE IN mm. DO NOT SCALE	IMPLIED TOLERANCES HOLE DIA AND LOCATIONS: ±0.5mm DIMENSIONS UP TO 30mm: ±1.5mm DIMENSIONS OVER 30mm: ±5% UP TO A MAX OF: ±5mm ANGULAR DIMENSIONS: ±5°	TCPN -	PART Alias UTX/DUL FGD1600-1640-8	TITLE FULL-TENSION GALVANISED-STEEL DEADEND (FGD) FITTING COND RANGE: Ø16.00-Ø16.40 LOOP 75				
DIST	—	I	NEW RELEASE	06-02-2014	AG	AT	MATERIAL DESC HEAVILY GALVANISED STEEL WIRE	MATL SPEC/STD/DRG NO -	PROCESS SPEC HEAT TREAT/PLATING NO -	Cat No FGD1600-1640-8	DRAWN AG	DATE 06-02-2014	TE Connectivity 2/3 Corella Close Berkeley Vale NSW 2261 Australia		
POS	REV	REVISION RECORD		DATE	DWN	APVD	MATERIAL NO -	MATL SPEC/STD/DRG NO -	PROCESS SPEC HEAT TREAT/PLATING NO -	SIZE A3	PROJECTION 3RD ANGLE	SCALE NTS	DRAWING NO FGD1600-1640-8-C	SHEET OF 1 1	REV 1